


| CATALOG NUMBER | PRIMARY VOLTAGE  | SECONDARY VOLTAGE                                    | 50/60 Hz 1 PHASE            |                 | APPROXIMATE WEIGHT (Lbs./Kg) |
|----------------|--|--|-----------------------------|-----------------|------------------------------|
|                |  |  | UL/cUL/CSA/NOM RATINGS (VA) | CE RATINGS (VA) |                              |
| 9070T50D19     | 208/240/277/380/480  | 24   | 50                          | 50              | 3.5 / 1.5                    |
| 9070T50D50     | 240/416/480/600<br>230/400/460/575<br>220/380/440/550<br>208/500 | 99/120/130<br>95/115/125<br>91/110/120<br>85/100/110 | 50                          | 50              | 4.0 / 1.8                    |



FILES/STANDARDS:  
 UL/cUL FILE: E61239  
 CSA FILE: LR37055  
 CE: TUV CERTIFIED TO 61558  
 NOM 117

50VA—CONTROL POWER TRANSFORMER  
 9070 TYPE T  
 CATALOG NUMBERS: FROM CHART



DWG# 5842  
 NO.