



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64

DUAL DIMENSIONS: INCHES
MILLIMETERS

POWER OUTLET CONFIGURATION	SERVICE	MAINS AMPERE RATING	CIRCUIT BREAKER (INCLUDED)	RECEPTACLES (INCLUDED) *	CATALOG NUMBER	MAIN WIRE SIZE (AWG)			
						PHASE AND NEUTRAL		EQUIPMENT GROUND	
						CU	AL	CU	AL
	120/240VAC 1Ø 3W	70	(1) Q0120GFI (1) Q0230GFI	(1) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 30A 125/250V 3W AND GROUND NEMA 14-30R	PAK31CGFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	70	(1) Q0120GFI (1) Q0220GFI	(1) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 20A 250V 2W AND GROUND NEMA 6-20R	PAK36C-1GFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	70	(1) Q0120GFI (1) Q0250GFI	(1) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 50A 250V 2W AND GROUND NEMA 6-50R	PAK51CGFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	70	(1) Q0120GFI (1) Q0250GFI	(1) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 50A 125/250V 3W AND GRD. NEMA 14-50R	PAK55CGFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	70	(2) Q0120GFI (1) Q0220GFI	(2) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 20A 250V 2W AND GROUND NEMA 6-20R	PAK72CGFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	70	(2) Q0120GFI (1) Q0250GFI	(2) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (1) 50A 125/250V 3W AND GROUND NEMA 14-50R	PAK76CGFI	#8-3	#8-3	(2) #14 OR 12	(2) #12 OR 10
	120/240VAC 1Ø 3W	100	(1) Q0120GFI (2) Q0250GFI	(1) 20A 125V 2W AND GROUND DUPLX NEMA 5-20R (2) 50A 125/250V 3W AND GROUND NEMA 14-50R	PAK1004CGFI	#8-2/0	#8-2/0	(2) #14 OR 12	(2) #12 OR 10

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-53303
NEUTRALS - INSULATED GROUNDABLE.
SUITABLE FOR USE AS TEMPORARY SITE SERVICE EQUIPMENT.
* ALL RECEPTACLES PROTECTED BY GFI BREAKERS.

SERVICE POWER OUTLET PANELS RAINPROOF NEMA TYPE 3R ENCLOSURE OUTDOOR	SQUARE D COMPANY
	DWG# 3261 NO.