



CATALOG NUMBER	PRIMARY VOLTAGE	SECONDARY VOLTAGE	50/60 Hz 1 PHASE		APPROXIMATE WEIGHT (Lbs/Kg)
			UL/cUL/CSA/NOM RATINGS (VA)	CE RATINGS (VA)	
9070T500D1	220/440 230/460 240/480	110 115 120	500	300	11.9 / 5.3
9070T500D2	240/480	24	500	300	11.9 / 5.3
9070T500D3	208	120	500	300	12.0 / 5.4
9070T500D4	277	120	500	300	11.8 / 5.3
9070T500D5	550 575 600	110 115 120	500	300	11.9 / 5.3
9070T500D12	440 460 480	220 230 240	500	300	11.9 / 5.3
9070T500D13	120	12/24	500	300	11.9 / 5.3
9070T500D14	208	24	500	300	11.7 / 5.3
9070T500D15	240/480	24/120	500	300	11.9 / 5.3
9070T500D22	480	277	500	300	11.8 / 5.3
9070T500D23	120/240	24	500	300	11.9 / 5.3
9070T500D24	110 115 120	110 115 120	500	300	11.9 / 5.3
9070T500D25	277	24	500	300	12.1 / 5.4
9070T500D31	220/440 230/460 240/480	110/220 115/230 120/240	500	300	11.6 / 5.2
9070T500D33	380/400/415	115/230	500	300	11.7 / 5.3
9070T500D36	600	12/24	500	300	11.6 / 5.2
9070T500D37	550 575 600	110/220 115/230 120/240	500	300	11.1 / 5.0
9070T500D52	380/400/415	12/24	500	300	12.1 / 5.4
9070T500D54	120/240	12/24	500	300	12.0 / 5.4
9070T500D55	110/220 115/230 120/240	110/220 115/230 120/240	500	300	11.5 / 5.2
9070T500D59	240/480	12/24	500	300	12.0 / 5.4
9070T500D60	277	120/240	500	300	11.8 / 5.3
9070T500D62	600	240	500	300	11.9 / 5.3



FILES/STANDARDS:

UL/cUL FILE: E61236
 CSA FILE: LR37055
 CE: TUV CERTIFIED TO 61558
 NOM 117

500VA-CONTROL POWER TRANSFORMER
 9070 TYPE T
 CATALOG NUMBERS: FROM CHART



DWG# 5900
 No.