# **Premium Power Protection**

APC Back-UPS Pro

APC Back-UPS Pro provide battery backup and surge protection ideal for your home, home office or small business.

The new Back-UPS Pro models are equipped with premium features including increased runtime and power capability for your critical electronics.



#### **Power and Protect**

#### Battery backup & surge protector outlets

Keep valuable devices running when the power is outside of safe levels

#### Sinewave power output\*

Ensures power quality without distortion or power drop during an outage. Ideal for advanced workstations, high end PCs, multimedia devices and home storage

#### 2 USB charging ports (Type C + Type A)\*

Fast charge mobile devices such as smartphones and tablets

#### AVR with boost and trim

Instantly corrects low/high voltage fluctuations and is Active Power Factor Correction (PFC) compatible

#### 1Gb network protection

Safeguards your equipment and valuable files from "back door" surges traveling along data lines without sacrificing internet speed

#### User replaceable batteries

Allows you to quickly replace batteries

#### LCD interface

Quick and easy to read, provides information about the utility and UPS conditions

#### PowerChute Serial Shutdown

Easy-to-use auto-shutdown software with power and energy management features

#### 2-3 year warranty

2 years repair or replace, 3 years repair and replace for European Union countries and UK

\*Only available for the BR-SI units\*

Ş

#### Pro Tip:

If you work remote or own a small business and rely on technology to keep you connected, then we recommend the SI models to ensure uptime and productivity.



BR1600SI

Life Is Or



## Certainty in a Connected World How much runtime will the Back-UPS Pro provide?

Connected Devices	Watt Load	BR650MI	BR900MI	BR1300MI	BR1600MI	BR1200SI	BR1600SI
Entry-level desktop PC with 20" monitor + internet modem and router	40 watts	64 mins	105 mins	141 mins	159 mins	124 mins	152 mins
iMac computer + NAS system + internet modem and router	119 watts	20 mins	34 mins	50 mins	57 mins	52 mins	67 mins
Gaming PC with 24" LCD monitor + external powered speakers + internet modem and router	240 watts	7 mins	14 mins	22 mins	26 mins	24 mins	32 mins
42" LCD television + sound bar + internet modem and router	335 watts	4 mins	8 mins	13 mins	17 mins	15 mins	21 mins





### APC Back-UPS Pro technical specifications Back-UPS Pro MI models



Product Specifications	BR650MI	BR900MI	BR1300MI	BR1600MI		
Output						
Power Capacity	390W/650VA	540W/900VA	780W/1300VA	960W/1600VA		
Output Voltage / Frequency (on utility)	196 to 264 Vac					
Out Voltage / Frequency (on battery)	230 V ± 8%, 50/60 Hz ± 1 Hz					
Output Connections (IEC)	6 battery backup with surge	e protection outlets (IEC)	8 total outlets: 6 battery backup with surge protection and 2 surge protection only (IEC)			
Waveform Type	Line Interactive/Stepped apprx sinewave					
Power Factor	0.6					
Input						
Input Voltage / Frequency	230 V nominal, 50/60 Hz ± 3 Hz					
Input Cord	6 ft cord, straight plug end with IEC outlet port					
Surge Protection						
Surge Energy Rating	557					
Dataline Surge Protection	1 Gb Dataline protection					
Overload Protection	On line: 10A circuit breaker, with overload warning capability On battery: internal current limit to overload alarm/shutdown					
Physical	•					
Unit Dimensions (HxWxD mm)	190x91	x310	250x100x382			
Unit Weight	6.4 kg	7 kg	10.2 kg	10.9 kg		
Shipping Dimensions (HxWxD mm)	255x440x143		330x485x225			
Shipping Weight	7.4 kg	8 kg	11.85 kg	11.65 kg		
RBC	APCRBC110	APCRBC164	APCRBC165	APCRBC166		
Runtime (full load)	3	3	4	4		
Runtime (half load)	10.5	11.4	10.6	10.4		
Color	Black					
Battery						
Battery Type	Lead acid					
Replacement Battery	Yes					
Management						
Alarms	On-battery, low battery warning, low battery shutdown, replace battery detected					
Shutdown Software		PCSS Soft	ware			
Conformance						
Certifications and Approvals	TDC lab: TUV GS, CB 60950 & 62040 Taiwan EMC lab: TelePermit Local Support: RCM, EAC, KETI, TISI					
Warranty and Equipment Protection	2 years repair or replace, 3 years repair and replace for European Union countries and UK					





## APC Back-UPS Pro technical specifications Back-UPS Pro SI models



Product Specifications	BR1200SI	BR1600SI			
Output					
Power Capacity	720W/1200VA	960W/1600VA			
	72007	300W/1000VA			
Output Voltage / Frequency (on utility)	196 to 264 Vac				
Out Voltage / Frequency (on battery)	230 V ± 8%, 50/60 Hz ± 1 Hz				
Output Connections (IEC)	8 total outlets: 6 battery backup and surge protection, 2 surge protection only				
Waveform Type	Line Interac	ctive/Sinewave			
Power Factor	0.6				
Input					
Input Voltage / Frequency	230 V nominal	, 50/60 Hz ± 3 Hz			
Input Cord	6 ft cord, straight plug	end with IEC outlet port			
Surge Protection					
Surge Energy Rating	557				
Dataline Surge Protection	1 Gb Dataline protection				
Overload Protection	On line: 10A circuit breaker, with overload warning capability On battery: internal current limit to overload alarm/shutdown				
Physical					
Unit Dimensions (HxWxD mm)	368x100x260				
Unit Weight	11.7 kg	12.1 kg			
Shipping Dimensions (HxWxD mm)		<223x482			
Shipping Weight	13.35 kg	13.75 kg			
RBC	APCRBC161	APCRBC163			
Runtime (full load)	4 14.2	4 22			
Runtime (half load) Color		l ZZ Slack			
Battery					
Battery Type		ad acid			
Replacement Battery	Yes				
Management					
Alarms	On-battery low battery warning low b	On-battery, low battery warning, low battery shutdown, replace battery detected			
Shutdown Software	PCSS Software				
	PCSS				
Conformance					
Certifications and Approvals	TDC lab: TUV GS, CB 60950 & 62040 Taiwan EMC lab: TelePermit Local Support: RCM, EAC, KETI, TISI				
Warranty and Equipment Protection	2 years repair or replace, 3 years repair and replace for European Union countries and UK				
L					



