



[Link to Thorsman cabling and fixing catalogue](#)



P147786

Thorsman cable ties

Description

- Cable ties are used for a wide range of applications including bundle up and fix cables, conduits and tubing
- Material PA6.6
- Available in black and clear colour
- Max operating temperature -40°C to +85°C
- Minimum installation temperature -20°C.

Application

- There are two types of Thorsman cable ties available:
 - made of clear polyamide, for indoor use
 - made of UV-stabilized black polyamide for both indoor and outdoor use.

+ Benefits

- The cable ties are self-locking. They cannot be opened and re-sealed.
- The cable ties have smooth rounded edges for easier handling and safer installation.
- The bent rounded tip allows easier insertion through the head of the cable tie.
- User friendly re-sealable packaging and documented quality.
- Manufactured and tested to EN62275, RoHS compliant.



P147787

Thorsman cable ties				
Type	Length (mm)	Colour	Qty per package	Ref. No.
Thorsman cable ties				
2.5 mm	100	Clear	100	IMT46026
		Black	100	IMT46033
	120	Clear	100	IMT46035
		Black	100	IMT46036
	160	Clear	100	IMT46074
		Black	100	IMT46073
200	Clear	100	IMT46158	
	Black	100	IMT46157	
3.6 mm	150	Clear	100	IMT46064
		Black	100	IMT46071
	200	Clear	100	IMT46149
		Black	100	IMT46156
	300	Clear	100	IMT46921
		Black	100	IMT46922
4.8 mm	200	Clear	100	IMT46101
		Black	100	IMT46118
	250	Clear	100	IMT46918
		Black	100	IMT46968
	300	Clear	100	IMT46919
		Black	100	IMT46969
370	Clear	100	IMT46248	
	Black	100	IMT46970	
7.6 mm	300	Black	100	IMT46923
	380	Clear	100	IMT46286
		Black	100	IMT46293
8.8 mm	550	Clear	100	IMT46926
		Black	100	IMT46924
	780	Black	100	IMT46927