

**CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC**Product  
ProduitName and address of the applicant  
Nom et adresse du demandeurName and address of the manufacturer  
Nom et adresse du fabricantName and address of the factory  
Nom et adresse de l'usineNote: When more than one factory, please report on page 2  
Note: Lorsque il y plus d'une usine, veuillez utiliser la deuxième pageRatings and principal characteristics  
Valeurs nominales et caractéristiques principalesTrademark (if any)  
Marque de fabrique (si elle existe)Type of Manufacturer's Testing Laboratories used  
Type de programme du laboratoire d'essais constructeurModel / Type Ref.  
Ref. De typeAdditional information (if necessary may also be reported on page 2)  
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la deuxième page)

A sample of the product was tested and found to be in conformity with

Un échantillon de ce produit a été essayé et a été considéré conforme à la

As shown in the Test Report Ref. No. which forms part of this Certificate

Comme indiqué dans le Rapport de tests numéro de référence qui constitue partie de ce Certificat

This CB Test Certificate is issued by the National Certification Body

Uninterruptible Power Supply

American Power Conversion Holdings Inc., Taiwan  
Branch  
3F., No.205, Sec. 3, Beixin Rd., Xindian Dist.,  
New Taipei City, 231  
TaiwanAmerican Power Conversion Holdings Inc., Taiwan  
Branch  
3F., No.205, Sec. 3, Beixin Rd., Xindian Dist.,  
New Taipei City, 231  
Taiwan Additional information on page 2Input: 5A, 220-240V, 1Ø, 50-60Hz AC output (UPS Outlet): 2.3A, 220-240V, 50-60Hz, 300W, 500VA for models BK500EI; BK500-RS; BK500.....; 1.6A, 220-240V, 50-60Hz, 210W, 350VA for model BK350.....; 1.5A, 220-240V, 50-60Hz, 195W, 325VA for model BK325I  
AC output (Surge Outlet): 2.3A, 220-240V, 50-60Hz, Cl. I.

BK500EI; BK500-RS; BK500.....; BK350.....; BK325I

The first three dots in the model name BK500..... can be 0 to 9, A to Z (but exclude combination of "EI" and "-RS"), "-" or blank, the last seven dots can be 0 to 9, A to Z, "-" or blank, for marketing use only. The dots in the model name BK350..... can be A to Z, 0 to 9, "-" or blank, for marketing use only.

 Additional information on page 2

IEC 62040-1:2008, IEC 62040-1:2008/AMD1:2013

358636

This certificate replaces the previous NO93605/M1, due to technical modifications and cancellation of one factory.

IEC

IECEE  
CB  
SCHEME

Ref. Certif. No.

NO93605/A1/M2

Ce Certificat de test OC est établi par l'Organisme National de Certification



Gaustadalléen 30  
NO-0373 Oslo, Norway

Date: 11-09-2018

A handwritten signature in blue ink, reading "Bård Myrvollen".

Signature: Bård Myrvollen  
Certification Department

DANAM PHILIPPINES INC.  
Philippines Economic Zone Authority (PEZA), Lot 1-A,  
Block 15, Phase III, Rosario, Cavite 4106  
Philippines

International Precision Assemblies, Inc. (Plant 3)  
Block 9 Phase 1, Road B, CEPZA, Rosario, Cavite  
Philippines

International Precision Assemblies, Inc. (Plant 2)  
Blk 17, Lot 2, Phase 4, CEPZA 4106, Rosario, Cavite  
Philippines

International Precision Assemblies, Inc. (Plant 1)  
Blk 8, Lot 6 East Avenue, Phase 1, CEPZA 4106  
Rosario, Cavite  
Philippines