

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OCProduct
ProduitName and address of the applicant
Nom et adresse du demandeurName and address of the manufacturer
Nom et adresse du fabricantName and address of the factory
Nom et adresse de l'usineNote: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la deuxième pageRatings and principal characteristics
Valeurs nominales et caractéristiques principalesTrademark (if any)
Marque de fabrique (si elle existe)Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur
Model / Type Ref.
Ref. De typeAdditional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la deuxième pageA sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à laAs shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport des essais numéro de référence qui constitue partie de ce Certificat

This CB Test Certificate is issued by the National Certification Body

Uninterruptible Power Supply

American Power Conversion Holdings Inc., Taiwan
Branch
3F., No.205, Sec. 3, Beixin Rd., Xindian Dist.,
New Taipei City 231
TaiwanAmerican Power Conversion Holdings Inc., Taiwan
Branch
3F., No.205, Sec. 3, Beixin Rd., Xindian Dist.
New Taipei City 231
Taiwan Additional information on page 2Input: 5A, 220-240V, 1Ø, 50-60Hz AC output (UPS Outlet): 2.3A, 220-240V, 50-60Hz, 300W, 500VA for models BK500EI; BK500-RS; BK500..... 1.6A, 220-240V, 50-60Hz, 210W, 350VA for model BK350..... 1.5A, 220-240V, 50-60Hz, 195W, 325VA for model BK325I
AC output (Surge Outlet): 2.3A, 220-240V, 50-60Hz Cl. I.

BK500EI; BK500-RS; BK500.....; BK350.....; BK325I

The first three dots in the model name BK500..... can be 0 to 9, A to Z (but exclude combination of "EI " and "-RS "), "-" or blank, the last seven dots can be 0 to 9, A to Z, "-" or blank, for marketing use only.
The dots in the model name BK350..... can be A to Z, 0 to 9, "-" or blank, for marketing use only. Additional information on page 2

IEC 62040-1(ed.1);am1

311969

Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 26-07-2016

Signature: Skule Moe
Certification Department

Ce Certificat de test OC est établi par l'Organisme National de Certification



Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 26-07-2016



Signature: Skule Moe
Certification Department

American Power Conversion
Lot 3 Block 14 Phase 3, PEZA Cavite Economic Zone,
Rosario Cavite
Philippines

International Precision Assemblies, Inc. (Plant 2)
Blk 17, Lot 2, Phase 4, CEPZA 4106, Rosario, Cavite
Philippines

International Precision Assemblies, Inc. (Plant 1)
Blk 8, Lot 6 East Avenue, Phase 1, CEPZA 4106
Rosario, Cavite
Philippines

DANAM PHILIPPINES INC.
Philippines Economic Zone Authority (PEZA), Lot 1-A,
Block 15, Phase III, Rosario, Cavite 4106
Philippines

International Precision Assemblies, Inc. (Plant 3)
Block 9 Phase 1, Road B, CEPZA, Rosario, Cavite
Philippines