



中国国家强制性产品认证证书

证书编号: 2005010309164811

委托人名称、地址

上海施耐德工业控制有限公司
中国上海市普陀区绥德路629号

生产者(制造商)名称、地址

上海施耐德工业控制有限公司
中国上海市普陀区绥德路629号

生产企业名称、地址

上海施耐德工业控制有限公司
中国上海市普陀区绥德路629号

产品名称和系列、规格、型号

热过载继电器

LRD33..C, LRE3.., LRE3..N, LRR3..N;详见附件

产品标准和技术要求

GB 14048.4-2010

上述产品符合强制性产品认证实施规则
CNCA-01C-011:2007的要求,特发此证。

发证日期: 2014年11月14日

有效期至: 2015年05月07日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书,证书首次颁发日期: 2005年11月17日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 1023346



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2005010309164811

NAME AND ADDRESS OF THE APPLICANT

Schneider Shanghai Industrial Control Co., Ltd.
No. 629 Suide Road, Putuo District, Shanghai, P. R. China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Shanghai Industrial Control Co., Ltd.
No. 629 Suide Road, Putuo District, Shanghai, P. R. China

NAME AND ADDRESS OF THE FACTORY

Schneider Shanghai Industrial Control Co., Ltd.
No. 629 Suide Road, Putuo District, Shanghai, P. R. China

NAME, MODEL AND SPECIFICATION

Thermal Overload Relay

LRD33..C, LRE3.., LRE3..N, LRR3..N, see the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4-2010

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-01C-011:2007).

Date of issue: Nov. 14, 2014 Date of expiry: May. 07, 2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Nov. 17, 2005

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>



Q 1023346



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2005010309164811

纸号: 1023346

LRD33..C, LRE3.., LRE3..N, LRR3..N

Ui:750V(LRD33..C,LRE3..,LRE3..N); 690V(LRR3..N)

Ue: AC660V;

Ie:17-25A, 23-32A, 30-40A, 37-50A,48-65A,55-70A, 63-80A, 80-104A;

脱扣级别: 10A;

3P;

外壳防护等级: IP20;

配用的辅助触头:(本体)

Ith:5A;

AC-15: 24V/4.16A, 48V/4.16A, 110V/3.63A, 230V/2.6A, 380V/1.58A,
400V/1.5A;

DC-13: 220V/0.20A;

1NO1NC

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



中国质量认证中心



王 王

主任



第 2 页 共 2 页

附录:

证书编号: 2005010309164811

纸号: 1023346

型号的解释:

<u>LRD</u>	<u>33</u>	<u>55</u>	<u>C</u>
I	II	III	IV

I	热过载继电器系列型号 LRD: 普通型热过载继电器 LRE: 优化型热过载继电器 LRR: 家用型热过载继电器
II	33: 普通型产品规格 3: 优化型产品规格
III	电流调整范围代号 22: 17-25A 53: 23-32A 55: 30-40A 57: 37-50A 59: 48-65A 61: 55-70A 63: 63-80A 65: 80-104A
IV	可选项 C: 中国制造普通型 (白色辅助触头端子盖) N: 中国制造优化型, 在中国销售的产品 (黑色辅助触头端子盖) 空白: 中国制造优化型、出口产品 (黑色辅助触头端子盖)

注: 此附录与证书同时使用时有效。

中国强制性产品认证标志

