



IP55

### Main

Electronic movement detector for outdoor ceiling mounting.  
360° surface monitoring over a length of 30 m and a width of 20 m.

### Complementary

- Operating elements for setting the brightness threshold and time.
- LED function display for fast alignment at the installation site.

**Mains voltage:** AC 230 V,  $\pm 10\%$ , 50 Hz

**Incandescent lamps:** max. 3000 W

**Halogen lamps:** AC 230 V, max. 2500 W

**Capacitive load:** max. 140  $\mu\text{F}$

**Max. switching current:** 16 A, AC 230 V,  $\cos\varphi = 0,6$

**Power consumption:** < 1 W

**Angle of detection:** 360°

**Range:** max. 16 m

**Number of levels:** 7

**Number of zones:** 124 with 496 switching segments

**Light sensor:** infinitely adjustable from 3-1000 lux

**Time:** adjustable in 6 levels of approx. 1 sec. to approx. 8 min.

**Neutral conductor:** required

**EC guidelines:** Low voltage guideline 73/23/EEC and EMC guideline 89/336/EEC

**Type of protection:** IP 55

**Accessories:** Capacitor, art. no. MTN542895.

Contents: With screws and plugs.

Colour: polar white