



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO154M200P	120/240VAC 1Ø 3W	200	54	72	#4-300
QO154M200PC					
QO154L225PG		225			
QO154L225PGC					
QO154L225PGMF					

NOTES:  
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
 UL LISTED - FILE E-6294  
 NEUTRALS - INSULATED GROUNDABLE.  
 LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.  
 LOAD CENTERS WITH "P" IN CATALOG NUMBER INCLUDE EXTENDED NEUTRALS FROM PLUG ON NEUTRAL READY INTERIORS.  
 LOAD CENTERS WITH "MF" IN CATALOG NUMBER ARE MONO-FLAT COVER COMPATIBLE.  
 LOAD CENTERS WITH "C" IN CATALOG NUMBER INCLUDE FLUSH/SURFACE MOUNTED COVER.

QO Plug-on Neutral Load Centers  
 GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE  
 INDOOR

**SQUARE D**  
 by Schneider Electric

DWG# PWFDS-SYRS-0057  
 NO.