



- NOTES:
- 1) IP20 TYPE ENCLOSURE
 - 2) AMBIENT TEMP 0-45 °C
 - 3) ALTITUDE 1000 m (3300 ft)
 - 4) HUMIDITY 95% NON-CONDENSING
 - 5) MINIMUM CLEARANCES 200 mm TOP AND BOTTOM

	Scale: 0.125	Tolerancing Standard : ISO8015		Units of measure : mm	
		ACCUSINE PCSN 60A 208-415V PH+N WM EXPAN PCSN060Y4W20E			
		Number: NVE9864001		Revision: 00	Sheet: 1/1
SQUARE D/SCHNEIDER ELECTRIC HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D/SCHNEIDER ELECTRIC AND MAY BE REPRODUCED OR USED ONLY IN ACCORDANCE WITH INSTRUCTIONS OR PERMISSION FROM SQUARE D/SCHNEIDER ELECTRIC. THIS DOCUMENT SHALL BE RETURNED TO SQUARE D/SCHNEIDER ELECTRIC UPON REQUEST. USER SHOULD VERIFY DRAWINGS ARE THE MOST RECENT VERSION PRIOR TO USE. © 2009 Schneider Electric, All Rights Reserved			State: Released for Manufacturing Printed on 2018/06/08		