



Main

Range	PowerLogic
Product or component type	Current transducer
Accessory / separate part category	Measurement accessory
Range compatibility	Acti 9 iEM3000 iEM3555 Acti 9 iEM3000 iEM3565 PowerLogic EM4200 EM4235 PowerLogic EM4200 EM4236 PowerLogic EM3500 EM3502A PowerLogic EM3500 EM3550A PowerLogic EM3500 EM3555A PowerLogic EM3500 EM3560A PowerLogic EM3500 EM3561A
Current transformer type	Flexible core

Complementary

Electrical connection	Flying lead 2.4 m 600 V
[In] rated current	50 mA...5000 A
Network frequency	50 Hz
Frequency measurement range	50 Hz...1.5 kHz
Measurement accuracy	1 %
Installation category	III
Pollution degree	2
Width	8 mm diameter
Height	305 mm opened
Diameter	98 mm

Environment

Standards	ANSI/IEEE C57.13
Product certifications	CE CURus UL recognized
Ambient air temperature for operation	-15...65 °C
Ambient air temperature for storage	-45...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.