



ATTESTATION of conformity with European Directives

BV LCIE CHINA Number N°2266AS07SDEC46161
Product EVlink Home
Reference See model list
Issued to Schneider Electric Industries SAS
Address 35, rue Joseph Monier 92500 Rueil Malmaison France
Manufacturer Schneider Electric Industries SAS
Technical characteristics See model list

The submitted sample of the above equipment has been tested for **CE** marking according to following European Directive and following standards:

LVD Directive 2014/35/EU

* Thanks to note that from April 20th 2016; this directive will be replaced by the new LVD directive, 2014/35/EU.

<i>Standards</i>	<i>Report number</i>	<i>Report date</i>
EN IEC 61851-1:2019	SDEC-ESH-P22031994	Jul.23th, 2022

The referred test report(s) show that the product complies with standard(s) recognized as giving presumption of compliance with the essential requirements in the specified European Directive

This verification does not imply assessment of the production of the product

The **CE** marking may be affixed if all relevant and effective European Directives with **CE** are applicable

Shanghai (P.R. China), Jul 28th, 2022



Denis SUN
Product Line Manager

This document shall not be reproduced, except in full, without the written approval of BV LCIE China. Information given in this document, are related to the tested specimen of the described electrical sample.

Model list

Model name	Input and output ratings	Connection method	Radio functions	Protection class	Mass
EVH4S03N2	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30℃ - 50℃	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S07N2	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30℃ - 50℃	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S11N2	Three phase, 11kw 380-415V, Max 16A,50Hz, -30℃ - 50℃	Case B T2 socket	NO	IP54 Class I	3.7kg
EVH4S03NC	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30℃ - 50℃	Case C Cable length:5m	NO	IP55 Class I	5.2kg
EVH4S07NC	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30℃ - 50℃	Case C Cable length:5m	NO	IP55 Class I	5.2kg
EVH4S11NC	Three phase, 11kw 380-415V, Max 16A,50Hz, -30℃ - 50℃	Case C Cable length:5m	NO	IP55 Class I	5.2kg