



DUAL DIMENSIONS: INCHES
MILLIMETERS

DEVICE	TYPE OF OPERATOR	CLASS 2510 TYPE	DIMENSIONS (IN.)		
			A	B	C
TYPE F	TOGGLE	FF1, 1P, 2, 2P FS1, 1P, 2, 2P	1.44	2.75	4.50
	KEY	FF3, 3P, 4, 4P FS3, 3P, 4, 4P	1.44	2.75	4.50
TYPE K	TOGGLE	KF1, 1A, 1B KF2, 2B, 2C KS1, 1A, 1B KS2, 2B, 2C	1.75	2.75	4.50
	KEY	KF3, 3A, 3B KF4, 4B, 4C KS3, 3A, 3B KS4, 4B, 4C	1.75	2.75	4.50

CATALOG NUMBER: 2510 FF, FS, KF, KS
 RATINGS: 1 HP FOR F 10 HP FOR K
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS LR25490 CLASS 3211 05
 WEIGHT: 2 LBS
 WIRE SIZE: FG=POWER #10 / KG VARIES PER MOTER SIZE/CONSULT NEC
 TERMINAL TORQUE: 20 LBS IN.

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FF_FS_KF_KS



DWG# 25100002
 NO.