



CATALOG NUMBER: 2510 FG
 RATINGS: 1 HP
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS: LR25490 CLASS 3211 05
 WEIGHT: 2 LBS
 WIRE SIZE: POWER #10
 TERMINAL TORQUE: 20 LBS IN.

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FG

SQUARE D
 Schneider Electric

DWG# 25100008
 NO.

DUAL DIMENSIONS: INCHES
 MILLIMETERS