



CATALOG NUMBER: 2510 FGJ/KGJ
 RATINGS: 1 HP FOR FG AND 10 HP FOR KG
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS: LR25490 CLASS 3211 05
 WEIGHT: 1.5 LBS
 WIRE SIZE: FG=POWER #10 / KG=VARIES PER MOTOR SIZE/CONSULT NEC
 TERMINAL TORQUE: 20 LBS IN.

DUAL DIMENSIONS: INCHES
MILLIMETERS

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FGJ_NEMA1_OVERSIZED



DWG# 25100010
 NO.