



CATALOG NUMBER: 2510 FW, KW
 RATINGS: 1 HP FOR F, 10 HP FOR K
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS: LR25490 CLASS 3211 05
 WEIGHT: 5 LBS
 WIRE SIZE: F=POWER #10 / K=VARIES PER MOTOR SIZE/CONSULT NEC
 TERMINAL TORQUE: 20 LBS IN.

DUAL DIMENSIONS: INCHES
 MILLIMETERS

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FW_KW_NEMA 4

SQUARE D
 Schneider Electric

DWG# 25100020
 NO.