



- (1) .75 COND TOP & BOTTOM (STD)
[19]
- (1) 1.50 COND TOP & BOTTOM (MAX)
[38]

CATALOG NUMBER: 2510 MBR
 RATINGS: 10 HP
 UL FILE/CCN: E78503 CCN NPXZ
 CSA FILE/CLASS: LR60905 CLASS 3218 04
 WEIGHT: 18 LBS
 WIRE SIZE: M,MOI #14 - #8
 TERMINAL TORQUE: 20 LBS IN
 WIRE SIZE: MIP #14 - #6
 TERMINAL TORQUE: 4 LBS IN

DUAL DIMENSIONS: INCHES
MILLIMETERS

NEMA INTEGRAL HORSEPOWER
 MANUAL STARTERS
 2510 MBR NEMA 7 & 9



DWG# 25100046
 NO.