


KNOCKOUTS				
SYMBOL	A	B	C	D
IN	.50	.75	1.00	1.25
MM	13	19	25	32



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG
QO2L40F QO2-4L70F/S	120/240VAC 1Ø 3W	40 70	2	2 4	#12-6 AL, #14-6 CU #12-3 AL, #14-4 CU

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
UL LISTED - FILE E-6294  
NEUTRALS - INSULATED GROUNDABLE.

QO LOAD CENTERS  
GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE - INDOOR

**SQUARE D COMPANY**

DWG. NO. **3018**