



KNOCKOUTS				
SYMBOL	A	B	C	D
IN	.50	.75	1.00	1.25
MM	13	19	25	32



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	MAIN WIRE SIZE AWG
QO260NATR	240VAC 1Ø 2W	60	10-4 AL/CU

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
UL LISTED - FILE E-59921  
MAXIMUM 10 HP, 240VAC  
USE SQUARE D TYPE QO200 MOLDED CASE SWITCH ONLY.

QO LOAD CENTERS  
RAINPROOF NEMA TYPE 3R ENCLOSURES - OUTDOOR

**SQUARE D COMPANY**

DWG. NO. 3103