




DRY-TYPE DRIVE ISOLATION TRANSFORMERS  
 93-145 KVA 3 Ø 60HZ  
 460V DELTA PRIMARY



IN EACH PHASE CONNECT TO TAP	
PRIMARY VOLTS	1-5% FCAN 1-5% FCBN
483	1
460	2
437	3

DUAL DIMENSIONS: INCHES  
MILLIMETERS

KVA	CATALOG NUMBER		GUAR. SOUND LEVEL	WGT. LBS	AVG % Z
	230Y SECONDARY	460Y SECONDARY			
93	93T144HDIT	93T145HDIT	50 DB	845	5.3
118	118T144HDIT	118T145HDIT	50 DB	920	5.5
145	145T144HDIT	145T145HDIT	50 DB	1025	5.4

NOTES:  
 UL LISTED  
 NEMA 2 VENTILATED ENCLOSURE  
 MINIMUM CLEARANCE OF 6.00 IN/152 MM MUST BE MAINTAINED  
 BETWEEN VENT OPENINGS AND OTHER OBSTRUCTIONS.  
 ALUMINUM WOUND  
 USE WEATHERSHIELD CAT WS380 FOR NEMA 3R OUTDOOR USE  
 220°C INSULATION SYSTEM FOR 150°C RISE  
 ▲ SPACE AVAILABLE IN BOTTOM FOR CUSTOMERS CONDUIT ENTRANCE.  
 ‡ SPACE AVAILABLE ON BOTH ENDS FOR CUSTOMERS CONDUIT.

DRY-TYPE DRIVE ISOLATION TRANSFORMERS  
 93-145 KVA 3 Ø 60HZ  
 460V DELTA PRIMARY



DWG. NO. 3687