



J:\wip\209\control online\5895.DWG 07/22/2008 12:17:48 PM

CATALOG NUMBER	PRIMARY VOLTAGE	SECONDARY VOLTAGE	50/60 Hz 1 PHASE		APPROXIMATE WEIGHT (Lbs/Kg)
			UL/cUL/CSA/NOM RATINGS (VA)	CE RATINGS (VA)	
9070T300D1	220/440 230/460 240/480	110 115 120	300	200	8.8 / 3.9
9070T300D2	240/480	24	300	200	8.8 / 3.9
9070T300D3	208	120	300	200	8.7 / 3.9
9070T300D4	277	120	300	200	8.7 / 3.9
9070T300D5	550 575 600	110 115 120	300	200	8.5 / 3.8
9070T300D12	440 460 480	220 230 240	300	200	8.8 / 3.9
9070T300D13	120	12/24	300	200	8.9 / 4.0
9070T300D14	208	24	300	200	8.6 / 3.9
9070T300D15	240/480	24/120	300	200	8.6 / 3.9
9070T300D22	480	277	300	200	8.1 / 3.7
9070T300D23	120/240	24	300	200	8.6 / 3.9
9070T300D24	110 115 120	110 115 120	300	200	8.7 / 3.9
9070T300D25	277	24	300	200	8.7 / 3.9
9070T300D31	220/440 230/460 240/480	110/220 115/230 120/240	300	200	8.6 / 3.9
9070T300D33	380/400/415	115/230	300	200	8.6 / 3.9
9070T300D36	600	12/24	300	200	9.2 / 4.1
9070T300D37	550 575 600	110/220 115/230 120/240	300	200	8.6 / 3.9
9070T300D52	380/400/415	12/24	300	200	8.5 / 3.8
9070T300D54	120/240	12/24	300	200	8.9 / 4.0
9070T300D55	110/220 115/230 120/240	110/220 115/230 120/240	300	200	8.6 / 3.9
9070T300D59	240/480	12/24	300	200	8.9 / 4.0
9070T300D60	277	120/240	300	200	8.8 / 3.9
9070T300D62	600	240	300	200	7.9 / 3.6



FILES/STANDARDS:
 UL/cUL FILE: E61239
 CSA FILE: LR37055
 CE: TUV CERTIFIED TO 61558
 NOM 117

300VA--CONTROL POWER TRANSFORMER
 9070 TYPE T
 CATALOG NUMBERS: FROM CHART



DWG# 5895
 NO.