


Telemecanique® *Phase™ Power Supply ABL7* Creator of energy



Wide offer of
single-phase
and three-phase
regulated switch
mode power
supplies from
0.3 A (7 W) to
40 A (960 W)





ABL7RM

- The ideal partner for the Zelio Logic Smart Relay
- 12 VDC and 24 VDC versions
- UL/CSA certifications



ABL7CEM

- Just one width offering interchangeability in all powers
- Connections permitting all types of cable ends (tags/plugs, etc.)
- UL certification
- The ideal partner for the Twido PLC



ABL7RE/RP

- The most compact offer of the market: 3 A / 72 W in 27 mm
- Anti-harmonics filter (PFC) according to EN 61000-3-2
- UL/CSA certifications

AS-IABL

- AS-Interface offer
- Earth fault management
- Mixed supply: AS-Interface (30 VDC) and control (24 VDC)



ABL7UES/UPS

- Compact offer thanks to “book” format
- Anti-harmonics filter (PFC) according to EN 61000-3-2
- Three-phase offers 400 to 520 VAC
- UL certification

Output voltage	Input voltage			
	100...240Vac	100...240Vac with PFC	3x400...520V with PFC	
24 Vdc	0.3 A	ABL7CEM24003		
	0.6 A	ABL7CEM24006		
	1.2 A	ABL7CEM24012		
	1.3 A modular	ABL7RM2401		
	2 A	ABL7RE2402		
	3 A	ABL7RE2403	ABL7RP2403	
	5 A	ABL7RE2405	ABL7RP2405	ABL7UES24050
	10 A	ABL7RE2410	ABL7RP2410	ABL7UPS24100
12 Vdc	1.9 A modular	ABL7RM1202		
	5 A		ABL7RP1205	
48 Vdc	3 A		ABL7RP4803	

Output voltage	for AS-Interface cable	Input voltage		
		100...240Vac AS-Interface	100...240Vac AS-Interface & 24Vdc	100...240Vac AS-Interface & DDT
24 Vdc	3 A		ASIABLM3024	
30 Vdc	2.4 A	ASIABLB3002	ASIABLM3024	ASIABLD3002
	4.8 A	ASIABLB3004		ASIABLD3004

Schneider Electric - North American Operating Division

1415 S. Roselle Road
 Palatine, IL 60067
 Tel: 847-397-2600
 Fax: 847-925-7500

www.us.telemecanique.com

Presentation, operating or usage characteristics of products presented in this document are subject to change at any time. Their description in no event constitutes a contractual obligation.