



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

9080LBA164101



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

For Use With:	Copper or Aluminum Wire
Terminal Type:	Lugs
Cover:	9080LB41
Service Class:	C
UL File:	E60616 XCFR2
CSA File:	70361 6228-01
RoHS:	Yes
CE Marked:	Yes
Flammability Rating:	UL94V-0
35mm Track Adapter:	N/A

Description:

Ampere Rating:
 Max. Voltage Rating:
 Number of Poles:
 Wire Range - Main:
 Wire Range - Branch:
 Short Circuit Current Ratings with Circuit Breakers:
 Short Circuit Current Ratings with Fuses:

Specification:

420A/340A (Cu/Al)
 600V AC/DC
 1
 (1)#4 to 600 AWG/kcmil
 (1)#4 to 600 AWG/kcmil
 N/A
 Up to 200kA