



by Schneider Electric

Basic Rack PDU


Overview

The APC by Schneider Electric Basic Rack PDU distributes power to devices in the rack.

Outlets. The Rack PDU has thirty-six (36) IEC 320-C13 outlets and 6 (6) IEC 320-C19 outlets.

Power cord. The 3-foot (0.91-meter) power cord terminates with a NEMA L21-20 connector.

AP7564



Specifications for AP7564

Electrical

Input connector	NEMA L21-20 plug
Output connectors	(36) IEC 320-C13 outlets (6) IEC 32-C19 outlets
Nominal input voltage	120/208 VAC 3-phase
Acceptable input voltage	± 10% of normal voltage
Input frequency	47–63 Hz

Physical

(H × W × D)	70.00×2.19×1.73 in (177.80×5.56×4.39 cm)
Shipping dimensions (H × W × D)	84.00×6.00×5.00 in (213.36×15.24×12.7 cm)
Weight	12 lb (5.44 kg)
Shipping weight	19.5 lb (8.85 kg)

Environmental

Maximum elevation (above MSL)	
Operating	15 000 ft (4500 m)
Storage	50 000 ft (15 000 m)
Temperature	
Operating	–5 to 45° C (23 to 115° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

Compliance

Safety verification	cULus
---------------------	-------

You can find customer support and warranty information on the APC website, www.apc.com.

© 2021 APC by Schneider Electric. All rights reserved.