

Easy UPS 3S Pro

To whom it may concern. This is to certify that Easy UPS 3S Pro is manufactured in the following country(ies):

UPSs

Commercial reference	Description	Country of origin	Manufacturing facility
E3SP10KH	Easy UPS 3S Pro 10 kVA 400 V 3:3 UPS for external batteries	China	Schneider Electric IT (China) Co., LTD.
E3SP15KH	Easy UPS 3S Pro 15 kVA 400 V 3:3 UPS for external batteries		
E3SP20KH	Easy UPS 3S Pro 20 kVA 400 V 3:3 UPS for external batteries		
E3SP30KH	Easy UPS 3S Pro 30 kVA 400 V 3:3 UPS for external batteries		
E3SP40KH	Easy UPS 3S Pro 40 kVA 400 V 3:3 UPS for external batteries		
E3SP15KHIN	Easy UPS 3S Pro 15 kVA 400 V India 3:3 UPS for external batteries		
E3SP20KHIN	Easy UPS 3S Pro 20 kVA 400 V India 3:3 UPS for external batteries		
E3SP30KHIN	Easy UPS 3S Pro 30 kVA 400 V India 3:3 UPS for external batteries		
E3SP40KHIN	Easy UPS 3S Pro 40 kVA 400 V India 3:3 UPS for external batteries		
E3SP10KHB	Easy UPS 3S Pro 10 kVA 400 V 3:3 UPS for internal batteries		
E3SP15KHB	Easy UPS 3S Pro 15 kVA 400 V 3:3 UPS for internal batteries		
E3SP20KHB	Easy UPS 3S Pro 20 kVA 400 V 3:3 UPS for internal batteries		
E3SP30KHB	Easy UPS 3S Pro 30 kVA 400 V 3:3 UPS for internal batteries		
E3SP40KHB	Easy UPS 3S Pro 40 kVA 400 V 3:3 UPS for internal batteries		
E3SP10K3I	Easy UPS 3S Pro 10 kVA 400 V 3:1 UPS for external batteries		
E3SP15K3I	Easy UPS 3S Pro 15 kVA 400 V 3:1 UPS for external batteries		
E3SP20K3I	Easy UPS 3S Pro 20 kVA 400 V 3:1 UPS for external batteries		
E3SP30K3I	Easy UPS 3S Pro 30 kVA 400 V 3:1 UPS for external batteries		
E3SP15K3IIN	Easy UPS 3S Pro 15 kVA 400 V India 3:1 UPS for external batteries		
E3SP20K3IIN	Easy UPS 3S Pro 20 kVA 400 V India 3:1 UPS for external batteries		
E3SP30K3IIN	Easy UPS 3S Pro 30 kVA 400 V India 3:1 UPS for external batteries		

Commercial reference	Description	Country of origin	Manufacturing facility
E3SP10K3IB	Easy UPS 3S Pro 10 kVA 400 V 3:1 UPS for internal batteries		
E3SP15K3IB	Easy UPS 3S Pro 15 kVA 400 V 3:1 UPS for internal batteries		
E3SP20K3IB	Easy UPS 3S Pro 20 kVA 400 V 3:1 UPS for internal batteries		
E3SP30K3IB	Easy UPS 3S Pro 30 kVA 400 V 3:1 UPS for internal batteries		
E3SP10KHB1	Easy UPS 3S Pro 10 kVA 400V 3:3 UPS, 1 internal 7Ah modular battery string, expandable to 3		
E3SP15KHB1	Easy UPS 3S Pro 15 kVA 400V 3:3 UPS, 1 internal 7Ah modular battery string, expandable to 3		
E3SP20KHB1	Easy UPS 3S Pro 20 kVA 400V 3:3 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP30KHB1	Easy UPS 3S Pro 30 kVA 400V 3:3 UPS, 2 internal 7Ah modular battery strings, expandable to 4		
E3SP40KHB1	Easy UPS 3S Pro 40 kVA 400V 3:3 UPS, 3 internal 7Ah modular battery strings, expandable to 4		
E3SP10KHB2	Easy UPS 3S Pro 10 kVA 400V 3:3 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP15KHB2	Easy UPS 3S Pro 15 kVA 400V 3:3 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP20KHB2	Easy UPS 3S Pro 20 kVA 400V 3:3 UPS, 3 internal 7Ah modular battery strings		
E3SP30KHB2	Easy UPS 3S Pro 30kVA 400V 3:3 UPS, 4 internal 7Ah modular battery strings		
E3SP40KHB2	Easy UPS 3S Pro 40 kVA 400V 3:3 UPS, 4 internal 7Ah modular battery strings		
E3SP10K3IB1	Easy UPS 3S Pro 10 kVA 400V 3:1 UPS, 1 internal 7Ah modular battery string, expandable to 3		
E3SP10K3IB2	Easy UPS 3S Pro 10 kVA 400V 3:1 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP15K3IB1	Easy UPS 3S Pro 15 kVA 400V 3:1 UPS, 1 internal 7Ah modular battery string, expandable to 3		
E3SP15K3IB2	Easy UPS 3S Pro 15 kVA 400V 3:1 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP20K3IB1	Easy UPS 3S Pro 20 kVA 400V 3:1 UPS, 2 internal 7Ah modular battery strings, expandable to 3		
E3SP20K3IB2	Easy UPS 3S Pro 20 kVA 400V 3:1 UPS, 3 internal 7Ah modular battery strings		
E3SP30K3IB1	Easy UPS 3S Pro 30 kVA 400V 3:1 UPS, 2 internal 7Ah modular battery strings, expandable to 4		
E3SP30K3IB2	Easy UPS 3S Pro 30 kVA 400V 3:1 UPS, 4 internal 7Ah modular battery strings		

Battery Solutions

Commercial reference	Description	Country of origin	Manufacturing facility
GVEBC7	Empty battery cabinet, 700 mm	China	Schneider Electric IT (China) Co., LTD.
GVEBC11	Empty battery cabinet, 1100 mm		
GVEBC15	Empty battery cabinet, 1500 mm		
E3SOPT007	Battery circuit breaker box		

Commercial reference	Description	Country of origin	Manufacturing facility
E3SOPT008	Battery circuit breaker kit		
E3SXR6	Modular battery cabinet		
E3SXR8	Modular battery cabinet		
E3SBTU	Battery module	Philippines	American Power Conversion Corporation (A.P.C.) B.V.
E3SBTHU	High capacity battery module		
E3SBT4	Battery string		
E3SBTH4	High capacity battery string		

Maintenance Bypass Panel

Commercial reference	Description	Country of origin	Manufacturing facility
E3SOPT006	Parallel maintenance bypass panel, 10-40 kVA	China	Schneider Electric IT (China) Co., LTD.
GVSBP5U10K20H	Maintenance bypass panel, single unit, 10 – 20 kVA 400 V wall-mount	India	Schneider Electric ITB (I) Pvt Ltd - Bangalore
GVSBP5U20K60H	Maintenance bypass panel, single unit, 20 – 60 kVA 400 V wall-mount		
GVSBP5U60K120H	Parallel maintenance bypass panel for 2 UPSs, 60 – 120 kVA 400 V wall-mount		
E3MBP50K400H	Maintenance bypass panel, single unit, 10 – 400 kVA 400 V wall-mount	China	Schneider Electric IT (China) Co., LTD.
E3MBP50K200H	Parallel maintenance bypass panel, 10 – 200 kVA 400 V wall-mount		

Options

Commercial reference	Description	Country of origin	Manufacturing facility
E3SOPT002	Parallel kit with 5 m cable	China	Schneider Electric IT (China) Co., LTD.
E3SOPT003	Temperature sensor kit for external battery system		
E3SOPT010	Dry contact card		
E3SOPT016	Parallel kit with 15 m cable		
E3SPOPT001	Cold start kit		
E3SPOPT002	Easy UPS 3S Pro 10-20 KVA 6-16 mm ² cable lug kit		
E3SPOPT003	Easy UPS 3S Pro 30-40 KVA 16-35 mm ² cable lug kit		
SP3OPT008	Backfeed box, 95 A 3-phase power contactor, bottom connection		
SP3OPT011	Regenerative energy braking box for external resistor bank, 50 Amps, 400 V		
SP3OPT012	Regenerative energy braking box for external resistor bank, 100 Amps, 400 V		
E3SOPT033	Regenerative box cable for UPS connection		