



Note:

- Drawings Not To Scale

Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Part No.:

ATS01N212QN

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Control Voltage: Weight [lb]/[kg]: UL File No.: CSA File: 110 - 240 Vac 0.93/0.42 E184727

224330

Other: IEC/EN 60947-4-2 CE,UL,CSA,C-Tick and CCC Specification:

Altistart 01 Soft Starters

Constant & Variable Torque

Description:
Family:
Product Line:
Application:
Output Ampere Rating:
hp rating 110V Single Phase: n/a
hp rating 208V Single Phase: n/a
kW rating 230V Single Phase: n/a
hp rating 230V Single Phase: n/a
kW rating 230V three Phase:
hp rating 230V three Phase:
hp rating 230V three Phase:
hp rating 460V three phase:
Enclosure Rating:

IP20

Enclosure Rating:

IP20