

EU DECLARATION OF CONFORMITY

We : Schneider Electric Industries SAS 35 rue Joseph Monier Rueil Malmaison 92500 – France

Hereby declare under our sole responsibility that the products:

Trademark	Schneider Electric
Product, Type	Altistart ATS480 & dedicated options VW3xxxx for soft starter
List of references and options	See next page

Are in conformity with the requirements of the following directives and conformity was checked in accordance with the following standards.

Directive	Harmonized standard
LV Directive 2014/35/EU	EN 60947-4-2: 2012 Low-Voltage switchgear and controlgear – Part 4-2: Contactors and motor-starters – AC
EMC Directive 2014/30/EU	semiconductor rmotor controllers and starters (IEC 60947-4-2: 2011)
European Directive 2011/65/EU -	EN IEC 63000:2018
"Restriction of Hazardous Substances" (RoHS) & Delegated Directive (EU) 2015/863 (RoHS 10)	Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances. Specific offer compliance information about RoHS are publicized on se.com

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions and to accepted rules of the art.

This declaration becomes invalid in the case of any modification to the products not authorized by us.

Compliance with the EMC Directive will require the application of the EMC guide giving requirements, details and advices for installation of products used.

The guides are available on https://www.se.com

Person in charge of technical documentation:

Frédéric Roussel, Schneider Toshiba Inverter Europe, rue André Blanchet, 27120 Pacy/Eure - France.

-DocuSigned by:

Main BERNERI)

Issued at Carros - FRANCE: 28/02/2022

Name : Alain BERNERD Industrial Control & Drives Customer Satisfaction & Quality

Vice President



EU DECLARATION OF CONFORMITY

Reference (1)

Power 208V - 600V	Current range
Control 110V – 230V	
ATS480D17Y	17 A
ATS480D22Y	22 A
ATS480D32Y	32 A
ATS480D38Y	38 A
ATS480D47Y	47 A
ATS480D62Y	62 A
ATS480D75Y	75 A
ATS480D88Y	88 A
ATS480C11Y	110 A
ATS480C14Y	140 A
ATS480C17Y	170 A
ATS480C21Y	210 A
ATS480C25Y	250 A
ATS480C32Y	320 A
ATS480C41Y	410A
ATS480C48Y	480A
ATS480C59Y	590A
ATS480C66Y	660A
ATS480C79Y	790A
ATS480M10Y	1000A
ATS480M12Y	1200A

⁽¹⁾ may be followed by 1 to 3 character.