



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2024010304660731

**NAME AND ADDRESS OF THE APPLICANT**

Schneider Electric (China) Co. Ltd. Shanghai Branch  
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

**NAME AND ADDRESS OF THE MANUFACTURER**

Schneider Electric Industries SAS  
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

**NAME AND LOCATION OF THE FACTORY**

PT. Schneider Electric Manufacturing Batam  
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning Kel.Muka Kuning  
Kec. Sungai Beduk – Batam, Indonesia

**PRODUCT NAME,MODEL AND SPECIFICATION**

Soft Starter  
ATS480D62Y 、 ATS480D75Y 、 ATS480D88Y 、 ATS480C11Y ;See the attachment for detailed  
parameters

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.6-2016

This is to certify that the above mentioned product(s) complies with the requirements of  
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** Jul.19,2024

**Valid until:** Jul.18,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to  
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



**SIGNATURE:**

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010304660731

Appendix: Page 1 of 1

ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y

Uimp: 6kV

Ui: 690V

Ith: 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),  
110A(ATS480C11Y)

Ue: AC208-690V

Ie: 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),  
110A(ATS480C11Y)

Pe: 11kW-45kW(ATS480D62Y), 15kW-55kW(ATS480D75Y),  
18.5kW-75kW(ATS480D88Y), 22kW-90kW(ATS480C11Y)

Utilization Category: AC-53a

Poles: 3P

IP20

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



# 中国国家强制性产品认证证书

证书编号：2024010304660731

认证委托人名称及地址

施耐德电气（中国）有限公司上海分公司  
上海市普陀区绥德路 669 号

生产者名称及地址

Schneider Electric Industries SAS  
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

PT. Schneider Electric Manufacturing Batam  
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning  
Kel. Muka Kuning Kec. Sungai Beduk - Batam, Indonesia

产品名称和系列、型号、规格

软起动器

ATS480D62Y 、ATS480D75Y 、ATS480D88Y 、ATS480C11Y ;详细参数见附页

产品标准和技术要求

GB/T 14048. 6-2016

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》  
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 19 日 有效期至：2029 年 07 月 18 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，  
也可在认监委网站（[www.cnca.gov.cn](http://www.cnca.gov.cn)）查询。



签发：

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





# 中国国家强制性产品认证证书

证书编号: 2024010304660731

证书附页: 第 1 页 共 1 页

型号: ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y

额定冲击耐受电压(Uimp): 6kV

额定绝缘电压(Ui): 690V

约定发热电流(Ith): 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),  
110A(ATS480C11Y)

额定工作电压(Ue): AC208-690V

额定工作电流(Ie): 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),  
110A(ATS480C11Y)

控制电动机的功率(Pe): 11kW-45kW(ATS480D62Y), 15kW-55kW(ATS480D75Y),  
18.5kW-75kW(ATS480D88Y), 22kW-90kW(ATS480C11Y)

使用类别: AC-53a

极数: 3P

IP20

ATS480	D62	Y
1	2	3

1	产品系列	ALTISTART 480
---	------	---------------

2	产品规格	62A    ATS480D62Y 75A    ATS480D75Y 88A    ATS480D88Y 110A    ATS480C11Y
---	------	---

3	电压等级	Y 控制电压 (208V 至 690V)
---	------	----------------------

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司