



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010304660708

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND LOCATION OF THE FACTORY

Wuxi Pro-face Co., Ltd
No. 20 Hanjiang Road, Wuxi, JiangSu, China

PRODUCT NAME,MODEL AND SPECIFICATION

Soft Starter
ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y ;See the attachment for detailed
parameters

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.6-2016

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.19,2024

Valid until: Jul.18,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010304660708

Appendix: Page 1 of 1

ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y
Uimp: 6kV;
Ui: 690V;
Ith:62A(ATS480D62Y),75A(ATS480D75Y),88A(ATS480D88Y),
110A(ATS480C11Y);
Ue: AC208-690V;
Ie: 62A(ATS480D62Y),75A(ATS480D75Y),88A(ATS480D88Y),
110A(ATS480C11Y);
Pe: 11kW-45kW(ATS480D62Y),15kW-55kW(ATS480D75Y),
18.5kW-75kW(ATS480D88Y),22kW-90kW(ATS480C11Y);
Utilization Category: AC-53a;
Poles: 3P;
IP20

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



中国国家强制性产品认证证书

证书编号：2024010304660708

认证委托人名称及地址

施耐德电气（中国）有限公司上海分公司
上海市普陀区绥德路 669 号

生产者名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

无锡普洛菲斯电子有限公司
江苏省无锡市汉江路 20 号

产品名称和系列、型号、规格

软起动器

ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y；详细参数见附页

产品标准和技术要求

GB/T 14048.6-2016

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 19 日 有效期至：2029 年 07 月 18 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010304660708

证书附页: 第 1 页 共 1 页

型号: ATS480D62Y、ATS480D75Y、ATS480D88Y、ATS480C11Y
额定冲击耐受电压(Uimp): 6kV;
额定绝缘电压(Ui): 690V;
约定发热电流(Ith): 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),
110A(ATS480C11Y);
额定工作电压(Ue): AC208-690V;
额定工作电流(Ie): 62A(ATS480D62Y), 75A(ATS480D75Y), 88A(ATS480D88Y),
110A(ATS480C11Y);
控制电动机的功率(Pe): 11kW-45kW(ATS480D62Y), 15kW-55kW(ATS480D75Y),
18.5kW-75kW(ATS480D88Y), 22kW-90kW(ATS480C11Y);
使用类别: AC-53a;
极数: 3P;
IP20

型号解释:

<u>ATS480</u>	<u>D62</u>	<u>Y</u>	
1	2	3	
1	产品系列	ALTISTART 480	
2	产品规格	62A	ATS480D62Y
		75A	ATS480D75Y
		88A	ATS480D88Y
		110A	ATS480C11Y
3	电压等级	Y 控制电压 (208V 至 690V)	

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司