



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]
 - Inch Dimensions are derived from the metric.

Part No.:
ATS48C17Y

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Control Voltage:	24v
Logic Input:	4
Analog Input:	1 PTC probe
Analog Output:	1
Logic/Relay Output:	3
Communication:	Modbus
Weight [lb]/[kg]:	27.3/12.4
UL File No.:	E184727
CSA File:	164581
Other:	IEC/EN 60947-4-2, EMC classes A & B, CE, DNV, C-Tick, GOST, CCC, NOM, SERPRO AND TCF

Specification:

Description:	
Family:	Altistart 48
Product Line:	Soft Starters
Application:	Constant & Variable Torque
Output Ampere Rating:	170A
Max. HP Rating 208V:	50
Max. HP Rating 230V:	60
Max. kW Rating 400V:	90
Max. HP Rating 460V:	125
Max. HP Rating 575V:	150
Enclosure Rating:	IP00
Frame Size:	C