



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]
 - Inch Dimensions are derived from the metric.

Part No.:
ATS48D38Y

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Control Voltage: 24v
 Logic Input: 4
 Analog Input: 1 PTC probe
 Analog Output: 1
 Logic/Relay Output: 3
 Communication: Modbus
 Weight [lb]/[kg]: 10.8/4.9
 UL File No.: E184727
 CSA File: 164581
 Other: IEC/EN 60947-4-2, EMC classes A & B, CE, DNV, C-Tick, GOST, CCC, NOM, SERPRO AND TCF

Specification:

Description:
 Family: Altistart 48
 Product Line: Soft Starters
 Application: Constant & Variable Torque
 Output Ampere Rating: 38A
 Max. HP Rating 208V: 10
 Max. HP Rating 230V: (1)
 Max. kW Rating 400V: 18.5
 Max. HP Rating 460V: 25
 Max. HP Rating 575V: 30
 Enclosure Rating: IP20
 Frame Size: A