



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BDA34050Y**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

**General Application:** Provides overload and short circuit protection  
**Approvals:** UL Listed - CSA Certified - IEC Rated  
**Mounting Type:** I-Line  
**Terminal Type:** ON end: I-Line / OFF end: Mechanical Lugs  
**Weight:** 3  
**Depth:**  
**Height:**  
**Width:**  
**Mounting Height:** 4.5

**Specification:**

**Description:** PowerPact B-Frame Thermal Magnetic Circuit Breaker  
**Number of Poles:** 3-Pole  
**Ampere Rating:** 050  
**Voltage Rating:** 480Y/277 VAC  
**Interrupting Rating:** 25kA at240VAC 18kA at480Y/277VAC  
**Circuit Breaker Rating:** 80% Rated  
**Fixed AC Magnetic Trip:** Hold: 480A - Trip: 720A