



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BDL36045



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

| | |
|----------------------|--|
| General Application: | Provides overload and short circuit protection |
| Approvals: | UL Listed - CSA Certified - IEC Rated |
| Mounting Type: | Unit Mount |
| Terminal Type: | ON end: EverLink Lugs / OFF end: EverLink Lugs |
| Weight: | 3 |
| Depth: | 4.01 |
| Height: | 6.22 |
| Width: | 6.22 |
| Mounting Height: | |

Specification:

| | |
|-------------------------|--|
| Description: | PowerPact B-Frame Thermal Magnetic Circuit Breaker |
| Number of Poles: | 3-Pole |
| Ampere Rating: | 045 |
| Voltage Rating: | 600Y VAC |
| Interrupting Rating: | 25kA at240VAC 18kA at480VAC 14kA at600Y/347VAC |
| Circuit Breaker Rating: | 80% Rated |
| Fixed AC Magnetic Trip: | Hold: 400A - Trip: 600A |