



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BDL36060LU



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application:	Provides overload and short circuit protection
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	Unit Mount
Terminal Type:	ON end: EverLink Lugs with Control Wire Terminal / OFF end: EverLink Lugs
Weight:	3
Depth:	4.01
Height:	6.22
Width:	6.22
Mounting Height:	

Specification:

Description:	PowerPact B-Frame Thermal Magnetic Circuit Breaker
Number of Poles:	3-Pole
Ampere Rating:	600
Voltage Rating:	600Y VAC
Interrupting Rating:	25kA at240VAC 18kA at480VAC 14kA at600Y/347VAC
Circuit Breaker Rating:	80% Rated
Fixed AC Magnetic Trip:	Hold: 640A - Trip: 960A