



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
CAD323BD

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Rating: A600, Q600 10A
UL File/CCN: E164862 / NKCR
CSA File: LR43364 3211 03
Meets Standards: IEC 60647-5
Weight: 1.28 lb (0.58 kg)
Termination Method: Spring Terminal
Wire Size: #14 - #18 AWG
Terminal torque: N/A
Mounting Hwd.: 35mm DIN Rail, #8 screw

Technical Information:

Description TeSys D IEC Control Relay - 3NO,2NC - Vdc Coil
Type TeSys D IEC Control Relay - 3NO,2NC - 24Vdc Coil
Voltages Code: BD at 24VDC
Coil Consumption: Inrush 5.4 W
 Sealed 5.4 W

Specification: