



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**CAD32MD**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating:	A600, Q600 10A
UL File/CCN:	E164862 / NKCR
CSA File:	LR43364 3211 03
Meets Standards:	IEC 60647-5
Weight:	1.28 lb (0.58 kg)
Termination Method:	Screw Clamp
Wire Size:	#10 - #18 AWG
Terminal torque:	15 lb-in (1.7 Nm)
Mounting Hwd.:	35mm DIN Rail, #8 screw

**Specification:**

Description	TeSys D IEC Control Relay - 3NO,2NC - Vdc Coil
Type	TeSys D IEC Control Relay - 3NO,2NC - 220Vdc Coil
Voltages Code:	MD at 220Vdc
Coil Consumption:	Inrush 5.4 W Sealed 5.4 W