



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**CAD503E7**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Rating:** A600, Q600 10A  
**UL File/CCN:** E164862 / NKCR  
**CSA File:** LR43364 3211 03  
**Meets Standards:** IEC 60647-5  
**Weight:** 1.28 lb (0.58 kg)  
**Termination Method:** Spring Terminal  
**Wire Size:** #14 - #18 AWG  
**Terminal torque:** N/A  
**Mounting Hwd.:** 35mm DIN Rail, #8 screw

**Technical Information:**

**Description** TeSys D IEC Control Relay - 5NO - Vac Coil  
**Type** TeSys D IEC Control Relay - 5NO - 48Vac Coil  
**Voltages Code:** E7 at 48Vac 50/60 Hz  
**Coil Consumption:** Inrush 70 VA  
 Sealed 8 VA

**Specification:**