



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
CAD50SL

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating:	A600, Q600 10A
UL File/CCN:	E164862 / NKCR
CSA File:	LR43364 3211 03
Meets Standards:	IEC 60647-5
Weight:	1.28 lb (0.58 kg)
Termination Method:	Screw Clamp
Wire Size:	#10 - #18 AWG
Terminal torque:	15 lb-in (1.7 Nm)
Mounting Hwd.:	35mm DIN Rail, #8 screw

Specification:

Description	TeSys D IEC Control Relay - 5NO - Vdc Coil
Type	TeSys D IEC Control Relay - 5NO - 72Vdc Coil
Voltages Code:	SL at 72Vdc
Coil Consumption:	Inrush 2.4 W Sealed 2.4 W