

Certificate Number: AZ 69026438

Page: 0002



CERTIFICATE OF APPROVAL

Authorised marking: TUV-026438-EA

CONTINUATION SHEET 1

(Modification 1)

The aim of this modification is to make the statement that the Certificate Approval AZ 69026438 cover the following models:

Schneider iC60N Series 1-63A 230/400V~,240/415V~, 6000A,

Curve B

Schneider iC60N Series 1-63A 230/400V~,240/415V~, 6000A,

Curve C

Schneider iC60N Series 1-63A 230/400V~,240/415V~, 6000A,

Curve D

Schneider iC60H Series 1-63A 230/400V~,240/415V~,10000A,

Curve B

Schneider iC60H Series 1-63A 230/400V~,240/415V~,10000A,

Curve C

Schneider iC60H Series 1-63A 230/400V~,240/415V~,10000A,

Curve D

Which are suitable for New Zealand market for household and similar installation.

Refer to Appendix verion 1.0 page 01 to 06 for model number and rating's details.

Issue Date: 24/04/2024

Expiry Date: 19/12/2027

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

A handwritten signature in blue ink, appearing to read 'Grant Li', positioned above a horizontal line.

Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60N Series 1-63A 230/400V~, 240/415V~, Icn: 6000A, Curve B

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 1P 1A B	A9F43101	iC60N 2P 1A B	A9F43201	1
iC60N 1P 2A B	A9F43102	iC60N 2P 2A B	A9F43202	2
iC60N 1P 3A B	A9F43103	iC60N 2P 3A B	A9F43203	3
iC60N 1P 4A B	A9F43104	iC60N 2P 4A B	A9F43204	4
iC60N 1P 6A B	A9F43106	iC60N 2P 6A B	A9F43206	6
iC60N 1P 10A B	A9F43110	iC60N 2P 10A B	A9F43210	10
iC60N 1P 16A B	A9F43116	iC60N 2P 16A B	A9F43216	16
iC60N 1P 20A B	A9F43120	iC60N 2P 20A B	A9F43220	20
iC60N 1P 25A B	A9F43125	iC60N 2P 25A B	A9F43225	25
iC60N 1P 32A B	A9F43132	iC60N 2P 32A B	A9F43232	32
iC60N 1P 40A B	A9F43140	iC60N 2P 40A B	A9F43240	40
iC60N 1P 50A B	A9F43150	iC60N 2P 50A B	A9F43250	50
iC60N 1P 63A B	A9F43163	iC60N 2P 63A B	A9F43263	63

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 3P 1A B	A9F43301	iC60N 4P 1A B	A9F43401	1
iC60N 3P 2A B	A9F43302	iC60N 4P 2A B	A9F43402	2
iC60N 3P 3A B	A9F43303	iC60N 4P 3A B	A9F43403	3
iC60N 3P 4A B	A9F43304	iC60N 4P 4A B	A9F43404	4
iC60N 3P 6A B	A9F43306	iC60N 4P 6A B	A9F43406	6
iC60N 3P 10A B	A9F43310	iC60N 4P 10A B	A9F43410	10
iC60N 3P 16A B	A9F43316	iC60N 4P 16A B	A9F43416	16
iC60N 3P 20A B	A9F43320	iC60N 4P 20A B	A9F43420	20
iC60N 3P 25A B	A9F43325	iC60N 4P 25A B	A9F43425	25
iC60N 3P 32A B	A9F43332	iC60N 4P 32A B	A9F43432	32
iC60N 3P 40A B	A9F43340	iC60N 4P 40A B	A9F43440	40
iC60N 3P 50A B	A9F43350	iC60N 4P 50A B	A9F43450	50
iC60N 3P 63A B	A9F43363	iC60N 4P 63A B	A9F43463	63

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60N Series 1-63A 230/400V~, 240/415V~, Icn: 6000A, Curve C

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 1P 1A C	A9F44101	iC60N 2P 1A C	A9F44201	1
iC60N 1P 2A C	A9F44102	iC60N 2P 2A C	A9F44202	2
iC60N 1P 3A C	A9F44103	iC60N 2P 3A C	A9F44203	3
iC60N 1P 4A C	A9F44104	iC60N 2P 4A C	A9F44204	4
iC60N 1P 6A C	A9F44106	iC60N 2P 6A C	A9F44206	6
iC60N 1P 10A C	A9F44110	iC60N 2P 10A C	A9F44210	10
iC60N 1P 16A C	A9F44116	iC60N 2P 16A C	A9F44216	16
iC60N 1P 20A C	A9F44120	iC60N 2P 20A C	A9F44220	20
iC60N 1P 25A C	A9F44125	iC60N 2P 25A C	A9F44225	25
iC60N 1P 32A C	A9F44132	iC60N 2P 32A C	A9F44232	32
iC60N 1P 40A C	A9F44140	iC60N 2P 40A C	A9F44240	40
iC60N 1P 50A C	A9F44150	iC60N 2P 50A C	A9F44250	50
iC60N 1P 63A C	A9F44163	iC60N 2P 63A C	A9F44263	63

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 3P 1A C	A9F44301	iC60N 4P 1A C	A9F44401	1
iC60N 3P 2A C	A9F44302	iC60N 4P 2A C	A9F44402	2
iC60N 3P 3A C	A9F44303	iC60N 4P 3A C	A9F44403	3
iC60N 3P 4A C	A9F44304	iC60N 4P 4A C	A9F44404	4
iC60N 3P 6A C	A9F44306	iC60N 4P 6A C	A9F44406	6
iC60N 3P 10A C	A9F44310	iC60N 4P 10A C	A9F44410	10
iC60N 3P 16A C	A9F44316	iC60N 4P 16A C	A9F44416	16
iC60N 3P 20A C	A9F44320	iC60N 4P 20A C	A9F44420	20
iC60N 3P 25A C	A9F44325	iC60N 4P 25A C	A9F44425	25
iC60N 3P 32A C	A9F44332	iC60N 4P 32A C	A9F44432	32
iC60N 3P 40A C	A9F44340	iC60N 4P 40A C	A9F44440	40
iC60N 3P 50A C	A9F44350	iC60N 4P 50A C	A9F44450	50
iC60N 3P 63A C	A9F44363	iC60N 4P 63A C	A9F44463	63

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60N Series 1-63A 230/400V~, 240/415V~, Icn: 6000A, Curve D

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 1P 1A D	A9F45101	iC60N 2P 1A D	A9F45201	1
iC60N 1P 2A D	A9F45102	iC60N 2P 2A D	A9F45202	2
iC60N 1P 3A D	A9F45103	iC60N 2P 3A D	A9F45203	3
iC60N 1P 4A D	A9F45104	iC60N 2P 4A D	A9F45204	4
iC60N 1P 6A D	A9F45106	iC60N 2P 6A D	A9F45206	6
iC60N 1P 10A D	A9F45110	iC60N 2P 10A D	A9F45210	10
iC60N 1P 16A D	A9F45116	iC60N 2P 16A D	A9F45216	16
iC60N 1P 20A D	A9F45120	iC60N 2P 20A D	A9F45220	20
iC60N 1P 25A D	A9F45125	iC60N 2P 25A D	A9F45225	25
iC60N 1P 32A D	A9F45132	iC60N 2P 32A D	A9F45232	32
iC60N 1P 40A D	A9F45140	iC60N 2P 40A D	A9F45240	40
iC60N 1P 50A D	A9F45150	-	-	50
iC60N 1P 63A D	A9F45163	iC60N 2P 63A D	A9F45263	63

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60N 3P 1A D	A9F45301	iC60N 4P 1A D	A9F45401	1
iC60N 3P 2A D	A9F45302	iC60N 4P 2A D	A9F45402	2
iC60N 3P 3A D	A9F45303	iC60N 4P 3A D	A9F45403	3
iC60N 3P 4A D	A9F45304	iC60N 4P 4A D	A9F45404	4
iC60N 3P 6A D	A9F45306	iC60N 4P 6A D	A9F45406	6
iC60N 3P 10A D	A9F45310	iC60N 4P 10A D	A9F45410	10
iC60N 3P 16A D	A9F45316	iC60N 4P 16A D	A9F45416	16
iC60N 3P 20A D	A9F45320	iC60N 4P 20A D	A9F45420	20
iC60N 3P 25A D	A9F45325	iC60N 4P 25A D	A9F45425	25
iC60N 3P 32A D	A9F45332	iC60N 4P 32A D	A9F45432	32
iC60N 3P 40A D	A9F45340	iC60N 4P 40A D	A9F45440	40
iC60N 3P 50A D	A9F45350	-	-	50
iC60N 3P 63A D	A9F45363	-	-	63

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60H Series 1-63A 230/400V~, 240/415V~, Icn: 10000A, Curve B

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 1P 1A B	A9F53101	iC60H 2P 1A B	A9F53201	1
iC60H 1P 2A B	A9F53102	iC60H 2P 2A B	A9F53202	2
iC60H 1P 3A B	A9F53103	iC60H 2P 3A B	A9F53203	3
iC60H 1P 4A B	A9F53104	iC60H 2P 4A B	A9F53204	4
iC60H 1P 6A B	A9F53106	iC60H 2P 6A B	A9F53206	6
iC60H 1P 10A B	A9F53110	iC60H 2P 10A B	A9F53210	10
iC60H 1P 16A B	A9F53116	iC60H 2P 16A B	A9F53216	16
iC60H 1P 20A B	A9F53120	iC60H 2P 20A B	A9F53220	20
iC60H 1P 25A B	A9F53125	iC60H 2P 25A B	A9F53225	25
iC60H 1P 32A B	A9F53132	iC60H 2P 32A B	A9F53232	32
iC60H 1P 40A B	A9F53140	iC60H 2P 40A B	A9F53240	40
iC60H 1P 50A B	A9F53150	iC60H 2P 50A B	A9F53250	50
iC60H 1P 63A B	A9F53163	iC60H 2P 63A B	A9F53263	63

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 3P 1A B	A9F53301	iC60H 4P 1A B	A9F53401	1
iC60H 3P 2A B	A9F53302	iC60H 4P 2A B	A9F53402	2
iC60H 3P 3A B	A9F53303	iC60H 4P 3A B	A9F53403	3
iC60H 3P 4A B	A9F53304	iC60H 4P 4A B	A9F53404	4
iC60H 3P 6A B	A9F53306	iC60H 4P 6A B	A9F53406	6
iC60H 3P 10A B	A9F53310	iC60H 4P 10A B	A9F53410	10
iC60H 3P 16A B	A9F53316	iC60H 4P 16A B	A9F53416	16
iC60H 3P 20A B	A9F53320	iC60H 4P 20A B	A9F53420	20
iC60H 3P 25A B	A9F53325	iC60H 4P 25A B	A9F53425	25
iC60H 3P 32A B	A9F53332	iC60H 4P 32A B	A9F53432	32
iC60H 3P 40A B	A9F53340	iC60H 4P 40A B	A9F53440	40
iC60H 3P 50A B	A9F53350	iC60H 4P 50A B	A9F53450	50
iC60H 3P 63A B	A9F53363	iC60H 4P 63A B	A9F53463	63

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60H Series 1-63A 230/400V~, 240/415V~, Icn: 10000A, Curve C

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 1P 1A C	A9F54101	iC60H 2P 1A C	A9F54201	1
iC60H 1P 2A C	A9F54102	iC60H 2P 2A C	A9F54202	2
iC60H 1P 3A C	A9F54103	iC60H 2P 3A C	A9F54203	3
iC60H 1P 4A C	A9F54104	iC60H 2P 4A C	A9F54204	4
iC60H 1P 6A C	A9F54106	iC60H 2P 6A C	A9F54206	6
iC60H 1P 10A C	A9F54110	iC60H 2P 10A C	A9F54210	10
iC60H 1P 16A C	A9F54116	iC60H 2P 16A C	A9F54216	16
iC60H 1P 20A C	A9F54120	iC60H 2P 20A C	A9F54220	20
iC60H 1P 25A C	A9F54125	iC60H 2P 25A C	A9F54225	25
iC60H 1P 32A C	A9F54132	iC60H 2P 32A C	A9F54232	32
iC60H 1P 40A C	A9F54140	iC60H 2P 40A C	A9F54240	40
iC60H 1P 50A C	A9F54150	iC60H 2P 50A C	A9F54250	50
iC60H 1P 63A C	A9F54163	iC60H 2P 63A C	A9F54263	63

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 3P 1A C	A9F54301	iC60H 4P 1A C	A9F54401	1
iC60H 3P 2A C	A9F54302	iC60H 4P 2A C	A9F54402	2
iC60H 3P 3A C	A9F54303	iC60H 4P 3A C	A9F54403	3
iC60H 3P 4A C	A9F54304	iC60H 4P 4A C	A9F54404	4
iC60H 3P 6A C	A9F54306	iC60H 4P 6A C	A9F54406	6
iC60H 3P 10A C	A9F54310	iC60H 4P 10A C	A9F54410	10
iC60H 3P 16A C	A9F54316	iC60H 4P 16A C	A9F54416	16
iC60H 3P 20A C	A9F54320	iC60H 4P 20A C	A9F54420	20
iC60H 3P 25A C	A9F54325	iC60H 4P 25A C	A9F54425	25
iC60H 3P 32A C	A9F54332	iC60H 4P 32A C	A9F54432	32
iC60H 3P 40A C	A9F54340	iC60H 4P 40A C	A9F54440	40
iC60H 3P 50A C	A9F54350	iC60H 4P 50A C	A9F54450	50
iC60H 3P 63A C	A9F54363	iC60H 4P 63A C	A9F54463	63

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

Appendix

Authorised marking: TUV-026438-EA

Version: 1.0

Issue date: 19-12-2022

Schneider iC60H Series 1-63A 230/400V~, 240/415V~, Icn: 10000A, Curve D

Single Pole 230/400V~,240/415V~		2 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 1P 1A D	A9F55101	iC60H 2P 1A D	A9F55201	1
iC60H 1P 2A D	A9F55102	iC60H 2P 2A D	A9F55202	2
iC60H 1P 3A D	A9F55103	iC60H 2P 3A D	A9F55203	3
iC60H 1P 4A D	A9F55104	iC60H 2P 4A D	A9F55204	4
iC60H 1P 6A D	A9F55106	iC60H 2P 6A D	A9F55206	6
iC60H 1P 10A D	A9F55110	iC60H 2P 10A D	A9F55210	10
iC60H 1P 16A D	A9F55116	iC60H 2P 16A D	A9F55216	16
iC60H 1P 20A D	A9F55120	iC60H 2P 20A D	A9F55220	20
iC60H 1P 25A D	A9F55125	iC60H 2P 25A D	A9F55225	25
iC60H 1P 32A D	A9F55132	iC60H 2P 32A D	A9F55232	32
iC60H 1P 40A D	A9F55140	iC60H 2P 40A D	A9F55240	40

3 Poles 400/415V~		4 Poles 400/415V~		Rated current In (A)
Reference No				
Generic	Commercial	Generic	Commercial	
iC60H 3P 1A D	A9F55301	iC60H 4P 1A D	A9F55401	1
iC60H 3P 2A D	A9F55302	iC60H 4P 2A D	A9F55402	2
iC60H 3P 3A D	A9F55303	iC60H 4P 3A D	A9F55403	3
iC60H 3P 4A D	A9F55304	iC60H 4P 4A D	A9F55404	4
iC60H 3P 6A D	A9F55306	iC60H 4P 6A D	A9F55406	6
iC60H 3P 10A D	A9F55310	iC60H 4P 10A D	A9F55410	10
iC60H 3P 16A D	A9F55316	iC60H 4P 16A D	A9F55416	16
iC60H 3P 20A D	A9F55320	iC60H 4P 20A D	A9F55420	20
iC60H 3P 25A D	A9F55325	iC60H 4P 25A D	A9F55425	25
iC60H 3P 32A D	A9F55332	iC60H 4P 32A D	A9F55432	32
iC60H 3P 40A D	A9F55340	iC60H 4P 40A D	A9F55440	40

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register