

IEC**IECEE**

®

TM

Ref. Certif. No.

CN51908

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Thermal Overload Relays

Name and address of the applicant

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the manufacturer

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

Schneider Electric a. s.
Cizovska 447 - 39701 Pisek - Czech Republic*Note: When more than one factory, please report on page 2*

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

LR2K0301, LR2K0302, LR2K0303,LR2K0304, LR2K0305, LR2K0306,
LR2K0307, LR2K0308, LR2K0310,LR2K0312, LR2K0314, LR2K0316,
LR2K0321, LR2K0322, LR7K0301,LR7K0302, LR7K0303, LR7K0304,
LR7K0305, LR7K0306, LR7K0307,LR7K0308, LR7K0310, LR7K0312,
LR7K0314, LR7K0316, LR7K0321, LR7K0322

Model / Type Ref.

Additional information (if necessary may also be reported on page 2)

IEC 60947-4-1:2018

A sample of the product was tested and found to be in conformity with

00901-CB2020CQC-092726

As shown in the Test Report Ref. No. which forms part of this Certificate

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Nov.30,2020

Signature:

Lu Mei

CB 0059311

LR2K0301, LR2K0302, LR2K0303,LR2K0304, LR2K0305, LR2K0306,
LR2K0307, LR2K0308, LR2K0310,LR2K0312, LR2K0314, LR2K0316,
LR2K0321, LR2K0322, LR7K0301,LR7K0302, LR7K0303,LR7K0304,
LR7K0305, LR7K0306, LR7K0307,LR7K0308, LR7K0310,LR7K0312,
LR7K0314, LR7K0316, LR7K0321,LR7K0322

Ui:690V;

Ue:690V;

Ie: 0.11-0.16A(LR2K only), 0.16-0.23A(LR2K only), 0.23-0.36A(LR2K only),
0.36-0.54A(LR2K only), 0.54-0.8A, 0.8-1.2A, 1.2-1.8A, 1.8-2.6A,
2.6-3.7A, 3.7-5.5A, 5.5-8A, 8-11.5A, 10-14A, 12-16A;

Tripping class:10A;

3P;

IP20

Auxiliary contacts:(body contact):

Ith:5A;

AC-15: Ue/Ie:240V/0.75A, 600V/0.3A;

DC-13:Ue/Ie:250V/0.11A;

1NO1NC

Page 1 of 1

Additional information (if necessary)

Date: Nov.30,2020

Signature:



Lu Mei