



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305659702

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND LOCATION OF THE FACTORY

PT. Schneider Electric Manufacturing Batam
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning Kel.Muka Kuning
Kec. Sungai Beduk – Batam, Indonesia

PRODUCT NAME,MODEL AND SPECIFICATION

Pushbutton and Pilot light

XB7E : Ui:250V;Uimp:4kV;AC-14:Ue/Ie:240V/0.3A,120V/0.6A;Ith:2A;Indicator light : Ue : Incandescent lamp : 250V
50~60Hz;Power supply by resistor : AC230V 50~60Hz;LED 灯 : AC120V 50~60Hz,AC230V 50~60Hz;IP54 (front),IP20
(back) ;Φ : 22.0mm

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.18,2024

Valid until: Jul.17,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659702

Appendix: Page 1 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

型号解释:

A) 按钮开关 Push buttons

$\frac{XB7EA}{I}$ $\frac{2}{II}$ $\frac{1}{III}$ $\frac{32}{IV}$ $\frac{P}{V}$ $\frac{3}{VI}$

I - 产品系列号及基本功能 Designate the series and the function:

XB7EA: 弹力恢复式按钮 Spring return push button

XB7EH: 自锁式按钮 Latching push button

XB7EL: 弹力恢复凸出式按钮 Spring return projecting push button

II - 操作头颜色 Colour of the head:

- 1 - 白色 White
- 2 - 黑色 Black
- 3 - 绿色 Green
- 4 - 红色 Red
- 5 - 黄色 Yellow
- 6 - 蓝色 Blue

III - 触头类型 Contacts:

- 1 - N/O
- 2 - N/C
- 3 - N/O + N/O
- 5 - C/O

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659702

Appendix: Page 2 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

IV - 按钮表面的记号 Type of marking on surface of the button:

(黑色/绿色/红色按钮→白色油墨; 白色按钮→黑色油墨; Black / Green / Red button → White ink ;

White button → Black ink)

- 31 - 标志“I” “I” symbol
- 32 - 标志“O” “O” symbol
- 33 - 标志“ARRET” 或“START” “ARRET” or “START” symbol
- 34 - 标志“STOP” “STOP” symbol
- 341 - 标志 向上箭头 up arrow
- 342 - 标志 向右箭头 right arrow
- 343 - 标志 向下箭头 down arrow
- 344 - 标志 向左箭头 left arrow
- 36 - 标志“II” “II” symbol
- 42 - 标志“MARCHE” “MARCHE” symbol

V - 扩展 Extension:

P - 型式 12 外壳及端子保护 For mounting on type 12 enclosure and terminals protection.

VI - 快速连接 Fast connection:

3 - 6.35mm 快速连接端子或 2 根 2.8mm 快速连接端子 Quick connect terminals of 6.35 mm or two times 2.8 mm

空白 - 螺纹连接端子 Or when blank - screw type terminals

B) 急停蘑菇头按钮开关 Emergency stop mushroom head Push buttons

| | | | | |
|-------------------|----------------|-----------------|----------------|---------------|
| $\frac{XB7ES}{I}$ | $\frac{1}{II}$ | $\frac{4}{III}$ | $\frac{2}{IV}$ | $\frac{P}{V}$ |
|-------------------|----------------|-----------------|----------------|---------------|

I - 基本功能 Function:

XB7ES: 急停蘑菇头按钮 Emergency stop mushroom head Push button

II - 操作头描述 Description of the head:

- 1 - 钥匙复位 Key to release
- 5 - 旋转复位 Turn to release

III - 操作头颜色 Colour of the head:

- 4 - 红色 Red

IV - 触头类型 Contacts:

- 2 - N/C
- 5 - N/C + N/O

V - 扩展 Extension:

P - 型式 12 外壳及端子保护 For mounting on type 12 enclosure and terminals protection.

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659702

Appendix: Page 3 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

C) 指示灯 Pilot light

| | | | | | |
|--------------|----------|----------|----------|----------|----------|
| <u>XB7EV</u> | <u>0</u> | <u>3</u> | <u>B</u> | <u>P</u> | <u>3</u> |
| I | II | III | IV | V | VI |

I - 基本功能 Function:

XB7EV: 指示灯 Pilot light

II - 电源 Supply:

0 - 整体式 LED 灯 Integral LED

6 - 直接供电, 白炽灯, 最大电压 250V, 50-60Hz, 灯泡功率最大 2.6W Direct supply, incandescent bulb, up to 250V, 50-60 Hz, lamp up to 2.6 W.

7 - 通过电阻供电, 白炽灯, 230V, 50-60Hz Direct through resistor, incandescent bulb, 230 V ac, 50-60 Hz

III - 颜色 Colour:

1 - 白色 White

3 - 绿色 Green

4 - 红色 Red

5 - 黄色 Yellow

6 - 蓝色 Blue

7 - 透明色 Clear

8 - 橙色 Orange

IV - LED 模块电压 Supply of LED models:

G - 120 V ac

M - 230 V ac

V - 扩展 Extension:

P - 型式 12 外壳及端子保护 For mounting on type 12 enclosure and terminals protection.

VI - 快速连接 Fast connection:

3 - 6.35mm 快速连接端子或 2 根 2.8mm 快速连接端子 Quick connect terminals of 6.35 mm or two times 2.8 mm

空白 - 螺纹连接端子 Or blank - screw type terminals

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.