



# 产品认证证书

证书编号: CQC2005010304140355

申请人名称及地址

施耐德电气(中国)有限公司上海分公司  
上海市普陀区绥德路669号

制造商名称及地址

Schneider Electric Industries SAS  
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

PT. Schneider Electric Manufacturing Batam(V049531)  
JI Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka  
Kuning Kel.Muka Kuning Kec. Sungai Beduk - Batam, Indonesia

产品名称和系列、规格、型号

报警信号灯柱及附件

XVM: Ui:250V;Uimp:4kV;Ue: AC120V,AC230V;XVM...F,XVM...H:IP54,XVM...(垂直安  
装):IP42,XVM...(其他安装位置):IP40;最大节数:5层(不含蜂鸣器基座),4层(含蜂鸣器  
基座);型号解释见附件

产品标准和技术要求

GB/T 14048.5-2017

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求,特发此证。

发证日期:2020年08月25日 有效期至:2024年02月27日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:



## 中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0372763



# PRODUCT CERTIFICATE

**CERTIFICATE NO.:** CQC2005010304140355

**NAME AND ADDRESS OF THE APPLICANT**

Schneider Electric (China) Co. Ltd. Shanghai Branch  
No. 669, Suide Road, Putuo District, Shanghai, China

**NAME AND ADDRESS OF THE MANUFACTURER**

Schneider Electric Industries SAS  
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

**NAME AND ADDRESS OF THE FACTORY**

PT. Schneider Electric Manufacturing Batam (V049531)  
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning Kel.Muka Kuning Kec. Sungai  
Beduk – Batam, Indonesia

**PRODUCT NAME, MODEL AND SPECIFICATION**

Beacons and indicator banks and accessories

XVM: Ui:250V;Uimp:4kV;Ue: AC120V,AC230V;XVM...F,XVM...H:IP54,XVM...(Vertical installation):IP42,XVM...(Other installation locations):IP40;Maximum number of nodes: 5 layers (excluding buzzer base), 4 layers (including buzzer base)

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

**TYPE OF CERTIFICATION SCHEMES**

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462142-2019 .

Valid from: Aug.25,2020

Valid until: Feb.27,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President: \_\_\_\_\_

Lu Mei



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

C 0372763





# 产品认证证书

附录

第 2 页 共 6 页

证书编号: CQC2005010304140355

纸号: 372763

B. 报警灯柱模块:

<u>XVM-C</u> I	<u>29</u> II	<u>B</u> III	<u>3T</u> IV
I-	产品基本型号 XVM C 系列报警灯柱模块		
II-	3 - 透镜 21 - 基座 + 盖 29 - 基座 + 蜂鸣器 + 盖		
III-	颜色 (对透镜) 3- 绿 4- 红 5- 琥珀 6- 蓝 7- 透明  电压 (对带有蜂鸣器的基座) G - 120V AC M - 230V AC		
IV-	固定基座 空白 - 不带固定基座 3T - 带 250mm 铝支撑管 + 金属支架		

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_

陆梅



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



# 产品认证证书

附录

第 3 页 共 6 页

证书编号: CQC2005010304140355

纸号: 372763

C. 灯泡:

	<u>DL</u> I	<u>2</u> II	<u>E</u> III	<u>D</u> IV	<u>B</u> V	<u>1</u> VI	<u>SB</u> VII
I-	产品基本型号 DL 系列插入式灯泡						
II-	功能 1- 白炽灯 2- LED 6- 放电管						
III-	系列 B- 标准系列 (放电管) E- 优化系列 (白炽灯或 LED)						
IV-	模式 (仅对白炽灯和 LED) D- 恒定光 K- 闪光灯						
V-	电压 G- 120V AC M- 230V AC						
VI-	颜色 (对 LED) 1- 白 3- 绿 4- 红 5- 黄 6- 蓝 7- 透明 8- 琥珀						
VII-	亮度 (仅对白炽灯和 LED) 空白- 普通亮度(LED) SB- 高亮度(LED) S- 白炽灯						

注: 此附录与证书同时使用时有效。

主任: 陆梅



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



# 产品认证证书

附录

第 4 页 共 6 页

证书编号: CQC2005010304140355

纸号: 372763

A. Complete products

XVM I	B II	I III	RG IV	S V	E VI	SB VII	01 VIII
I-	Product basic designation XVM series beacons and indicator banks						
II-	Supply Voltage G - 120 V AC M - 230 V AC						
III-	Function 1-Incandescent bulb 2-LED						
IV-	Color and type of signaling unit for each level (Up to 5 levels of signaling units without buzzer base; only allow 4 levels of signaling units when with buzzer base)  Color for each level signaling unit: R - Red A - Amber G - Green B - Blue C - Clear  Type for each level signaling unit: Blank - Steady light 5 - Flashing Light 6 - Discharge Tube Bulb						
V-	Buzzer S - With Buzzer Base Blank - Without Buzzer Base						
VI-	Assembly Conditions: Blank - With aluminium support tube 250mm + metal bracket (IP42 mounted vertically, and IP40 mounted in other positions) H - With aluminium support tube 250mm + plastic fixing base (IP54) F - With aluminium support tube 100mm + plastic fixing base(IP54) W - With plastic fixing base (IP42 mounted vertically, and IP40 mounted in other positions)						
VII-	Brightness Blank - Normal brightness SB - Super brightness						

注: 此附录与证书同时使用时有效。

主任: 陆梅



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



# 产品认证证书

附录

第 5 页 共 6 页

证书编号: CQC2005010304140355

纸号: 372763

B. Indicating bank modules:

<u>XVM C</u> I	<u>29</u> II	<u>B</u> III	<u>3T</u> IV
I-	Product basic designation XVM C series indicating bank modules		
II-	3 - Lens 21 - Base + Cover 29 - Base + Buzzer + Cover		
III-	Color (lens only) 3- Green 4- Red 5- Amber 6- Blue 7- Clear  Supply Voltage (for base with built-in buzzer only) G - 120V AC M - 230V AC		
IV-	With Fixing Base Blank - Without any fixing base 3T - With aluminium support tube 250mm + metal bracket		

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_

陆梅



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



# 产品认证证书

附录

第 6 页 共 6 页

证书编号: CQC2005010304140355

纸号: 372763

C. Plug-in bulbs:

	$\frac{DL}{I}$	2 II	E III	D IV	B V	1 VI	SB VII
I-	Product basic designation DL series plug-in bulbs						
II-	Function 1 - Incandescent bulb 2 - LED 6- Discharge Tube Bulb						
III-	Series B - Standard series (discharge tubes) E - Optimum series (incandescent or LED bulbs)						
IV-	Mode (for incandescent and LED only) D - Steady Light K - Flashing Light						
V-	Supply Voltage G - 120V AC M - 230V AC						
VI-	Colour (for LED Only) 1 - White 3 - Green 4 - Red 5 - Yellow 6 - Blue 7 - Clear 8 - Amber						
VII-	Brightness (for incandescent or LED bulbs) Blank - Normal brightness (for LED bulbs) SB - Super brightness (for LED bulbs) S- incandescent bulbs						

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>