

# FLS10-20LED Slimline LED Floodlights

## FLS10LED – 10 Watt LED Floodlight

**Specification:** Charcoal Grey Die Cast Aluminium Body with Stylish Silver Trim, IP65, Tempered Glass.  
10 Watt, 720 Lumens, Efficacy 72 Lumens/Watt  
Lamp Colour Temp 4000 ° Kelvin, Lamp Life 36,000 hrs (L70)

**Dimensions:** Body & Bracket – Width 152mm, Height 130mm, Depth 25mm

**Typical Use:** Domestic applications where the customer wants a stylish option that is more aesthetically pleasing to the eye.  
For areas approximately 6m x 6m depending on application.  
Mounting height generally from 3 to 4 metres high.  
Suitable for above the barbeque or under the pergola.  
(No real comparison to older style existing product).



## FLS20LED – 20 Watt LED Floodlight

**Specification:** Charcoal Grey Die Cast Aluminium Body with Stylish Silver Trim, IP65, Tempered Glass.  
20 Watt, 1600 Lumens, Efficacy 80 Lumens/Watt  
Lamp Colour Temp 4000 ° Kelvin, Lamp Life 36,000 hrs (L70)

**Dimensions:** Body & Bracket – Width 213mm, Height 180mm, Depth 28mm

**Typical Use:** Domestic applications where the customer wants a stylish option that is more aesthetically pleasing to the eye.  
For areas approximately 10m x 10m depending on application.  
Mounting height generally from 3 to 5 metres high.

**Comparison:** Similar in coverage to old Par38 flood lamp which was originally 150W Incandescent and then became 120W Tungsten Halogen, 23W Compact Fluorescent and 18-20W LED versions.  
FLS20LED would be considered a general equivalent to all of these.



For more information contact your Clipsal and Schneider Electric Partner Business Representative or visit [clipsal.com](http://clipsal.com)

© 2015 Schneider Electric. All Rights Reserved. All trademarks owned by Schneider Electric

**CLIPSAL**<sup>®</sup>

by Schneider Electric