

PRODUCT DATA SHEET



Application:

This enclosure is designed for the increased need for the average family household to distribute services such as Free to Air TV, pay TV, DVD, video recorders, surveillance cameras, distributed audio solutions, Internet (wired and wireless versions), data networking and telephone services. Switches, modems and routers can be installed inside the enclosure freeing up space on desks.

This enclosure only comes complete with the following:

- 1 x 10 pair telephone disconnection module and mount
- 1 x communication earthing point
- 1 x Twin Vertical Switched Socket Outlet
- 400mm rubber grommet for cable entries
- fixing screws
- legend card.

Dimensions:

Overall – 524mm Wide x 954mm High

Enclosure – 465mm Wide x 895mm High x 117mm Deep.

Cut out – 470mm Wide x 900mm High.

PRODUCT DATA SHEET



Features:

- 1st fix mounting or 2nd fix mounting tabs – unique to Clipsal
- reversible door hinging left or right hand side
- same size and look as the 60 Pole electrical Switch board (product family)
- multiple cable anchor points
- segregated power zone for 240Volt power packs (standards compliant)
- 240 twin Switched Socket outlet and mounting accessories
- long mounting rails for VDU's and other StarServe and audio accessories
- large cable entry above mounting rails for TV cabling (no bending radius issues)
- ample room for StarServe accessories when fully fitted out
- provision for up to 48 Clipsal Keystone Data outlets (Cat 5e or Cat6).
- no bending radius issues for data cabling (Cat 5e or Cat6).
- separate cabling zone for telephone and data cables
- hinged escutcheon for ease of data patch panel termination
- angled escutcheon for patch lead bending radius.

Accessories Sold Separately:

| Data Outlets | Keystone Cat 5e | Keystone Cat 6 |
|--|---------------------------------|--------------------|
| | RJ88SMA5,BK | RJ88SMA6,BK |
| Fast Ethernet Switches | 5 Port | 8 Port |
| | 95ESW5P10/ | 95ESW8P10/ |
| Patch Leads | Cat 5e | Cat 6 |
| 0.5m | RJ5A8/05PL | RJ6A8/05PL |
| 1.0m | RJ5A8/10PL | RJ6A8/10PL |
| 1.5m | RJ5A8/15PL | RJ6A8/15PL |
| 2.0m | RJ5A8/20PL | RJ6A8/20PL |
| 3.0m | RJ5A8/30PL | RJ6A8/30PL |
| Switch Bracket / Cradle | 3105SWBKT | |
| VDU - Type | VDU | IR Engine |
| 2 input – 6 output | 8072/6VHP | NO |
| 3 input – 8 output | 8073/8VHPIR | YES |
| 2 input – 4 output (combination telephone) | 3105VDU24T | NO |
| 3 input – 8 output (combination telephone) | 3105VDU38IRT | YES |
| Audio Accessories | Audio Distribution Junction Box | Audio Power supply |
| | 3105ADJB | 3105APS24V |
| Modulator Type | Modulator | IR Distribution |
| Single Channel Stereo | 8071VMS | YES |
| Single Channel Mono | 8071VMP | NO |
| 2 Channel Mono | 8072VMPIR | YES |
| 4 Channel Mono | 8074VMPIR | YES |