


Insulated Plug 10A, 20A 500V Models 4, 5 and 7 Pin

Installation Instructions

WIPxxxB Series



1. Unscrew gland nut with complete gland assembly intact. Loosen cord clamp.
2. Place hand over pin surround. Lever out C-Clip, being careful not to lose spring clip.
3. Remove plug pin housing assembly from plug body.
4. Strip flexible cord as shown, pass through gland nut, cable gland and plug body.
5. Place appropriate conductors into plug pin housing assembly terminals and tighten screws to secure bared conductors and ensure good electrical contact. Check Earth is connected to E terminal.
6. Pull excess cord in plug cover until pin housing assembly seats itself in cover. Re-insert C-Clip spring.
7. Screw gland nut tight to ensure IP rating is maintained.
8. To lock gland nut in place terminate locking screw into recess provided.
9. Tighten clamp onto cord.

This product is designed to effectively clamp and seal on cable outside diameters as listed. Other devices such as cable glands, flexible conduit adaptors etc. may be used and will need to have the thread form shown to suit the product.

Cat. No.	Description	Max Cable O.D.	Min Cable I.D.	Alt Entry Thread Form
WIP410B	4 Pin 10A, 500V	11.5	7.3	M32 x 1.5
WIP420B	4 Pin 20A, 500V	13.5	9	M32 x 1.5
WIP510B	5 Pin 10A, 500V	13.5	9	M32 x 1.5
WIP520B	5 Pin 20A, 500V	16.5	11	M32 x 1.5
WIP720B	7 Pin 20A, 500V	16.5	11	M32 x 1.5

Product of Clipsal Australia Pty Ltd

A member of Schneider Electric

Contact us: clipsal.com/feedback

National Customer Care Enquiries:

Tel 1300 2025 25

Fax 1300 2025 56

clipsal.com

Clipsal Australia Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this catalogue are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© Clipsal Australia Pty Ltd. The identified trademarks and copyrights are the property of Clipsal Australia Pty Ltd unless otherwise noted.