



P D L

NEW PRODUCT DATA AND APPLICATION SHEET

CATALOGUE #
666TMB24WH

BARCODE #
9416175130281

DESCRIPTION White 24V DC surface mount Buzzer Module



BOX QUANTITY 20

OUTER QUANTITY Nil

FEATURES

24V DC Piezo buzzer.
Plate depth, fully modular product for surface mounting in standard 600 series plates.
Current - 20mA (at rated voltage).
Sound Pressure - 90dB (at rated voltage).
Nominal frequency - 3100 Hz.
Rated for continuous use.
Twin terminals accept up to 0.5mm² single strand cables or up to 1mm² multi-strand cable.

APPLICATIONS

Nurse call or other applications where ELV buzzers are a requirement.
Surface mount ability increases versatility.

COMMENTS

666TMB24 performs equally to the also available – 566MNCB 24V DC buzzer