



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010305659648

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND LOCATION OF THE FACTORY

PT. Schneider Electric Manufacturing Batam
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning Kel.Muka Kuning
Kec. Sungai Beduk – Batam, Indonesia

PRODUCT NAME,MODEL AND SPECIFICATION

Indicator Light

XVB : Ui:250V; Uimp:4kV; XVBC3.:Ue:AC24-48V,48-230V, XVBC4.:Ue:AC24-48V,48-230V, XVBC2.:Ue:
AC120V,AC230V, XVBC5.:Ue:AC120V,AC230V; IP65(mounted on fixing base), IP66(mounted directly on base
unit) ; See the Appendix for type explanation

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.18,2024

Valid until: Jul.17,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659648

Appendix: Page 1 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

型号解释:

白炽灯型号规格解释

<u>XVB</u> I	<u>C</u> II	<u>4</u> III	<u>B</u> IV	<u>3</u> V
I -	产品系列号 XVB			
II -	外形			
III -	C - 镜片或底座 + 盖 为可层层叠加的信号灯			
	灯泡型式和信号型式			
	3 - 白炽灯, 恒定光			
	4 - 白炽灯, 闪烁光			
IV -	21 - 底座 + 盖 + 垫圈 为标准型底部电缆插口			
	电源电压 (仅适用于闪烁型光)			
	B - 24...48 V DC			
	M - 48...230 V AC			
V -	镜片颜色			
	3 - 绿色			
	4 - 红色			
	5 - 琥珀色			
	6 - 蓝色			
	7 - 透明			
	8 - 黄色			

LED 型和放电管型号规格解释

<u>XVB</u> I	<u>C</u> II	<u>5</u> III	<u>B</u> IV	<u>3</u> V
I -	产品系列号 XVB			
II -	形状			
III -	C - 镜片或 底座 + 盖 为可层层叠加的信号灯			
	灯泡型式和信号型式或其它			
	2 - 集成 LED 恒定光			
	5 - 集成 LED 闪烁光			
	21 - 底座和盖 + 垫圈 为标准型底部电缆插口			
IV -	07 - 底座和垫圈 为闪烁光			
	电压 (仅适用于闪烁光)			
	G - 120 V AC			
	M - 230 V AC			
V -	镜片颜色			
	3 - 绿色			
	4 - 红色			
	5 - 琥珀色			
	6 - 蓝色			
	7 - 透明			
	8 - 黄色			

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659648

Appendix: Page 2 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

Description of the series		Incandescent Pilot Light Models				
Explanation about the model		XVB	C	4	B	3
		I	II	III	IV	V
I	Series designation XVB					
II	Shape C - Lens or base + cover for bank					
III	Type of bulb and type of signal or other 3 - Incandescent bulb, steady light 4 - Flashing with incandescent bulb 21 - Base + cover + gasket with bottom or side cable entry for standard type					
IV	Supply Voltage (for flashing type only) B - 24...48 VDC M - 48...230 VAC					
V	Lens Color 3 - Green 4 - Red 5 - Amber 6 - Blue 7 - Clear 8 - Yellow					

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010305659648

Appendix: Page 3 of 3

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

Description of the series		LED Cluster models and built-in strobe models				
Explanation about the model		XVB	C	5	B	3
		I	II	III	IV	V
I	Series designation					
	XVB					
II	Shape					
	C - Lens or base + cover for bank					
III	Type of bulb and type of signal or other					
	2 - Integrated LED (steady light)					
	5 - Integrated LED (flashing light)					
	21 - Base + cover + gasket with bottom or side cable entry for standard type					
	07 - Base and gasket for strobe type					
IV	Supply Voltage (for flashing type only)					
	G - 120 VAC					
	M - 230 VAC					
V	Lens Color					
	3 - Green					
	4 - Red					
	5 - Amber					
	6 - Blue					
	7 - Clear					
	8 - Yellow					

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.