

Product data sheet

Characteristics

D224N

Safety switch, general duty, fusible, 200A, 2 pole, 60hp, 240VAC, NEMA 1, neutral factory installed



Product availability: Stock - Normally stocked in distribution facility

Price*: 884.00 USD



Main

Product or Component Type	Single Throw Safety Switch
Series name	General duty
Device Application	Residential
Disconnecter device type	Fusible disconnect switch
Device Composition	Neutral (factory installed)
Phase	1 phase
Number of poles	2
Line Rated Current	200 A
[Ue] rated operational voltage	240 V AC
NEMA degree of protection	NEMA 1
Motor power hp	15 Hp at 240 V AC 60 Hz for 1 phase motors 25 Hp at 240 V AC 60 Hz for 3 phase motors 60 Hp at 240 V AC 60 Hz for 3 phase motors

Complementary

Short-circuit current	100 KA maximum depending on fuse H, K or R
Fuse type	H, K or R
Device mounting	Surface
Electrical Connection	Lugs
Wiring configuration	3-wire
AWG gauge	AWG 6...250 kcmil aluminium/copper
Tightening torque	275 Lbf.In (31.07 N.m) (AWG 6...250 kcmil)
Depth	8.25 In (209.55 mm)
Width	19 In (482.60 mm)
Height	29 In (736.60 mm)
Net Weight	53.51 Lb(US) (24.27 kg)

Environment

Product Certifications	UL listed file E2875
------------------------	----------------------

Ordering and shipping details

Category	US1DE1A00006
Discount Schedule	DE1A
GTIN	785901460749
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.10 In (20.574 cm)
Package 1 Width	30.50 In (77.47 cm)
Package 1 Length	19.30 In (49.022 cm)
Package 1 Weight	41.80 Lb(US) (18.96 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**