



ELECTRICAL CLEARANCE/WIRE BENDING SPACE



MINIMUM TO WALL OR BARRIER TO INSURE ADEQUATE
WIRE BENDING SPACE TO LUG SURFACE WHEN
THE MAXIMUM WIRE SIZE IS USED. REF. NEC 43D-10



NEMA SIZE 00 CONTACTOR
3-POLE PDLYPHASE - 600 VAC, 50-60 HZ

COIL VOLTAGE CODE (1)	VOLTAGE	
	60 HZ	50 HZ
V01	24	-
V02	120	110
V08	208	-
V03	240	220
V06	480	440
V07	600	550
V99	SPECIFY	SPECIFY

Catalog Number: B502-SE02(1)
 Ratings: SEE CHART
 UL File/CCN: E78351/NLX
 CSA File/Class: LR60905/3211 0
 Meets Standards: -
 Weight: 13.2 lbs
 Wire Size: POWER - #14-#1/D I CONTRL - #16-#12
 Terminal torque: 100 LB-IN
 Mounting hwd.: (3) 1/4" screws

DUAL DIMENSIONS: INCHES
MILLIMETERS

NEMA SIZE 3 CONTACTOR
CLASS B502 TYPE SE02(1)



DWG# E0300501-01
NO.